

OP-TS-3 SPECIFICATIONS

OP LINK HOME AUTOMATION KITS - TRIPLESIELD

Secure Your Home Or Business With a Complete Self-monitoring System



Key Features

- Group Video Alarm & Alerts
- Instant Video Alarm And Alerts To Family And Friends Simultaneously Upon Sensor
- Trigger From Multiple Locations
- Entire Solution Controlled By Free Smart Phone App
- Extend & Expand System With Add-Ons
- Plug-Activate-N-Play™ Gets You Up And Running In Minutes



Multi User



Groups Of Alarm/Alerts



Multi-Site



24/7 Monitoring



Instant Notification



QR Code Setup


Smart Phone App To Remotely Control System




Smart phone App




- SYSTEM ARMING & DISARMING
- STAY MODE



- POWER MANAGEMENT
- REMOTE POWER ON/OFF



- INSTANT LIVE STREAMING
- MULTI-SITE & SINGLE VIDEO VIEW



- EVENT TRIGGERED PUSH NOTIFICATION
- EVENT HISTORY LISTING


The entire solution is controlled through an easy-to-use FREE Smartphone App, giving you complete control, anywhere there is an internet connection.

Plug And Play Setup



1

Plug.
Connect & Power Up Devices



2

Activate.
Download Free Mobile App & Start Device Activation



3

Play.
Zero - Configuration. System is Ready

OP-TS-3 SPECIFICATIONS

OP LINK HOME AUTOMATION KITS

1 x Wi-Fi IP Cam Kit



WHAT'S INSIDE:

- 1 x OPU2120
- 1 x Wi-Fi IP Cam
- 2 x Door/Window Sensor
- 1 x Siren
- 1 x 16GB USB Flash Drive

Specifications:

OPLINK PROCESSING UNIT (OPU)	
WI-FI WIRELESS	
Wi-Fi Frequency	2.4~2.4835GHz
Wireless Standard	IEEE802.11B/G/N
Sensitivity	<65dbm, 11g@54mbps
TX Power	11.5dBm±2dBm, 11g@54Mbps
Antenna	External, 2.5dBi
RF WIRELESS	
RF Frequency	433.92MHz
Sensitivity	-106dBm±1dBm
Antenna	External, 2dBi
Output Power to Antenna	-4dBm±1dBm
IP CAMERA	
WI-FI WIRELESS	
Wi-Fi Frequency	2.4~2.4835GHz
Wireless Standard	802.11b: 18 dBm (Max.) 802.11g: 14 dBm (Max.) 802.11n20: 13 dBm (Max.) 802.11n40: 13 dBm (Max.)
Antenna Gain	3.9dBi, chip antenna

DOOR/WINDOW SENSOR	
RF WIRELESS	
RF Frequency	433.92MHz ±150KHz
Modulation	ASK
Antenna	Internal Antenna
Transmit Power	-16dBm
SIREN	
RF WIRELESS	
RF Frequency	433.92MHz ±0.125MHz
Sensitivity	-110dBm
Modulation	ASK
Antenna	Internal Antenna