



IEC Mineral Insulated Thermocouples with PFA Lead

Types 'K' or 'J' with 1 metre PFA Lead & Bare Tails - Stainless Steel Sheath



(Note: Illustration shows Type 'K')

- Mineral insulated Thermocouple to IEC 584
- Choice of Type 'K' with 310 stainless steel sheath or Type 'J' with 321 stainless steel sheath
- Highly flexible, sheath can be bent/formed to suit many applications and processes
- Insulated hot junction
- Plain pot seal (200°C)
- 1 metre 7/0.2mm PFA Teflon® insulated flat pair cable and tails (colour coded to IEC 584)
- Manufactured using materials to IEC 584 class 1 specification

Specifications

Sensor type: Type 'K' (Nickel Chromium/Nickel Aluminium)

Type 'J' (Iron/Constantan)

Construction: Flexible mineral insulated probe with stainless steel sheath, plain pot seal & 1

metre extension cable

Manufactured: Tolerances of materials used in the manufacture conform to class 1 specification

to relevant BS EN 60584 standards.

Element/hot junction: Single element, junction insulated from sheath (offers protection against spurious

electrical signals)

Termination: 1 metre 7/0.2mm PFA Teflon® insulated flat pair cable, colour coded in

accordance with IEC 584

Probe temperature range: Type 'K' -40°C to +1100°C >1.0mm diameter

-40°C to +750°C – 1.0mm diameter and below

Type 'J' -40° C to $+750^{\circ}$ C

Pot seal rating: 200°C

Type 'K' - 310 stainless steel sheath:

Good corrosion & oxidation resistance to suit a wide range of processes, satisfactorily operates in sulphur bearing atmospheres

Typical applications include brick & cement kilns, glass industry, heat treatment & annealing furnaces, power stations, flues, heat exchangers etc.

T/C Type	Probe Dia. (mm)	Probe Length (mm)	Cable jacket	Tails: +pos/-neg	order code
K	1.0	500	Green	Green/White	XF-1057-FAR
K	1.0	1000	Green	Green/White	XF-1055-FAR
K	1.0	2000	Green	Green/White	XF-1058-FAR
K	1.5	500	Green	Green/White	XF-1059-FAR
K	1.5	1000	Green	Green/White	XF-1062-FAR
K	1.5	1500	Green	Green/White	XF-1060-FAR
K	3.0	1000	Green	Green/White	XF-1064-FAR
K	4.5	150	Green	Green/White	XF-1065-FAR

Type 'J' - 321 stainless steel sheath:

Excellent corrosion resistance, retains good ductile properties to suit a wide range of industrial applications & processes Typical applications include heat treatment & annealing furnaces, aluminium heat treatment, chemical reactors, plastic/rubber moulding industry, polythene manufacture, coal plants, paper mills, textile industry etc.

T/C Type	Probe Dia. (mm)	Probe Length (mm)	Cable jacket	Tails +pos/-neg	order code
J	1.5	150	Black	Black/White	XF-1048-FAR
J	1.5	250	Black	Black/White	XF-1049-FAR
J	3.0	150	Black	Black/White	XF-1050-FAR
J	3.0	250	Black	Black/White	XF-1051-FAR
J	6.0	150	Black	Black/White	XF-1052-FAR
J	6.0	250	Black	Black/White	XF-1053-FAR