Product datasheet Characteristics

XS1M18AB120

inductive sensor XS1 M18 - L53mm - brass - Sn5mm - 12..24VDC - cable 2m



Main

Wichin		:
Range of product	OsiSense XS	
Series name	Application	{5}
Sensor type	Inductive proximity sensor	- 5
Device application	-	— 2
Sensor name	XS1	
Sensor design	Cylindrical M18	<u>a</u>
Size	53 mm	5
Body type	Fixed	— —
Detector flush mounting acceptance	Flush mountable	- 0
Material	Metal	
Type of output signal	Analogue	}
Wiring technique	2-wire	ţ
[Sn] nominal sensing distance	5 mm	— <u>s</u>
Discrete output function	1 NC	
Output circuit type	DC	2.
Analogue output range	420 mA	
Electrical connection	Cable	_ q
Cable length	2 m	——————————————————————————————————————
[Us] rated supply voltage	1224 V DC	_ ;
IP degree of protection	IP67 conforming to IEC 60529	
		— į

Complementary

M18 x 1	
Frontal	
PPS	
Nickel plated brass	F
0.55 mm	
	Frontal PPS Nickel plated brass

Repeat accuracy	<= 3% of Sr
Linearity error	+/- 2 mA
Cable composition	3 x 0.34 mm ²
Wire insulation material	PvR
Supply voltage limits	1038 V DC
Switching frequency	<= 500 Hz
Current consumption	4 mA at no-load
Output current drift	<= 10 %
Marking	CE
Threaded length	44 mm
Height	18 mm
Length	53 mm
Product weight	0.12 kg

Environment

Product certifications	CSA UL
Ambient air temperature for operation	-2570 °C


Offer Sustainability

Sustainable offer status	Green Premium product	
RoHS (date code: YYWW)	Compliant - since 0811 - Schneider Electric declaration of conformity	
	Schneider Electric declaration of conformity	
REACh	Reference not containing SVHC above the threshold	
	Reference not containing SVHC above the threshold	
Product environmental profile	Available	
	Product environmental	
Product end of life instructions	Available	
	🚰 End of life manual	

Contractual warranty

Warranty period	18 months	

Dimensions




(1) LED

Product datasheet Mounting and Clearance

XS1M18AB120


Minimum Mounting Distances

Side by side




e (1) ≱0 mm/0.39 in.

Face to face



e (2) ≱60 mm/2.36 in. Facing a metal object




e (3) ≱5 mm/0.60 in

Product datasheet Mounting and Clearance

XS1M18AB120

Mounting




(1) Bending cable: 4 x external cable diameter

Product datasheet Connections and Schema

XS1M18AB120

Wiring Schemes

2-Wire connection




(1) Output current

BN : Brown BK : Black BU : Blue

	Output current	Load impedance value
12 V	420 mA	R ≤ 8.2 Ω
24 V	420 mA	R ≤ 470 Ω

XS1M18AB120

Output Curves



- (Y) Is (mA)
- (X) Sensors object distance (mm)