## Product datasheet Characteristics

## **RE17LAMW**

on-delay timing relay - 1 s..100 h - 24..240 V AC/ DC - solid state output



#### Main

IVIAII I	
Range of product	Zelio Time
Product or component type	Modular timing relay
Discrete output type	Solid state
Width	17.5 mm
Component name	RE17L
Time delay type	A
Time delay range	110 s 110 h 660 min 0.11 s 660 s 10100 h 110 min
Nominal output current	0.7 A
Component name Time delay type Time delay range	RE17L  A  110 s  110 h  660 min  0.11 s  660 s  10100 h  110 min

### Complementary

Control type	Selector switch on front panel
[Us] rated supply voltage	24240 V AC/DC at 50/60 Hz
Voltage range	0.851.1 Us
Supply frequency	5060 Hz (+/- 5 %)
Impulse duration	0.05 s typical
Insulation resistance	100 MOhm at 500 V DC conforming to IEC 60664-1
[Uimp] rated impulse withstand voltage	5 kV (1.2/50 µs)
Delay response	< 100 ms
Connections - terminals	Screw terminals, clamping capacity: 1 x 0.51 x 3.3 mm² AWG 20AWG 12 (solid) without cable end  Screw terminals, clamping capacity: 2 x 0.52 x 2.5 mm² AWG 20AWG 14 (solid) without cable end  Screw terminals, clamping capacity: 1 x 0.21 x 2.5 mm² AWG 24AWG 14 (flexible) with cable end  Screw terminals, clamping capacity: 2 x 0.22 x 1.5 mm² AWG 24AWG 16 (flexible) with cable end
Tightening torque	0.61 N.m conforming to IEC 60947-1

Dielectric strength	2.5 kV 1 mA/1 minute 50 Hz conforming to IEC 61812-1
Housing material	Self-extinguishing
Repeat accuracy	+/- 0.5 % conforming to IEC 61812-1
Temperature drift	+/- 0.05 %/°C
Voltage drift	+/- 0.2 %/V
Setting accuracy of time delay	+/- 10 % of full scale at 25 °C conforming to IEC 61812-1
Reset time	350 ms on de-energisation typical
On-load factor	100 %
Power consumption in VA	<= 3 VA at 240 V AC
Power consumption in W	<= 1.5 W at 240 V DC
Breaking capacity	0.5 A AC/DC conforming to UL 0.7 A AC/DC at 20 °C
Operating rate in Hz	10 Hz
Maximum output current	20 A <= 10 ms
Minimum switching current	10 mA
Leakage current	< 5 mA
Maximum switching voltage	250 V AC/DC
Voltage drop	4 V 3-wire 8 V 2-wire
Electrical durability	100000000 cycles
Marking	CE
Creepage distance	4 kV/3 conforming to IEC 60664-1
Safety reliability data	MTTFd = 353.8 years B10d = 320000
Mounting position	Any position in relation to normal vertical mounting plane
Mounting support	35 mm DIN rail conforming to EN/IEC 60715
Product weight	0.068 kg

### Environment

<= 20 ms
5 mA/°C
2006/95/EC EN 61000-6-1 2004/108/EC EN 61000-6-4 EN 61000-6-3 EN 61000-6-2 IEC 61812-1
CSA cULus GL
-3060 °C
-2060 °C
IP20 (terminal block) conforming to IEC 60529 IP40 (housing) conforming to IEC 60529 IP50 (front panel) conforming to IEC 60529
20 m/s² (f = 10150 Hz) conforming to IEC 60068-2-6
15 gn (duration = 11 ms) conforming to IEC 60068-2-27
93 % without condensation conforming to IEC 60068-2-30
Electrostatic discharge immunity test, in contact at 6 kV conforming to IEC 61000-4-2 level 3 Electrostatic discharge immunity test, in air at 8 kV conforming to IEC 61000-4-2 level 3 Susceptibility to electromagnetic fields, 80 MHz to 1 GHz at 10 V/m conforming to IEC 61000-4-3 level 3 Electrical fast transient/burst immunity test, capacitive connecting clip at 1 kV conforming to IEC 61000-4-4 level 3 Electrical fast transient/burst immunity test, direct at 2 kV conforming to IEC 61000-4-4 level 3 1.2/50 µs shock waves immunity test, differential mode at 1 kV conforming to IEC 61000-4-5 level 3 1.2/50 µs shock waves immunity test, common mode at 2 kV conforming to IEC 61000-4-5 level 3 Conducted RF disturbances, 0.1580 MHz at 10 V conforming to IEC 61000-4-6 level 3

Voltage dips and interruptions immunity test, 1 cycle at 0 % conforming to IEC 61000-4-11 Voltage dips and interruptions immunity test, 25/30 cycles at 70 % conforming to IEC 61000-4-11 Conducted and radiated emissions conforming to EN 55022 class B

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1243 - Schneider Electric declaration of conformity
	Schneider Electric declaration of conformity
REACh	Reference not containing SVHC above the threshold
	Reference not containing SVHC above the threshold

# Product datasheet Technical Description

## **RE17LAMW**


### Function A: Power on Delay Relay

#### Description

The timing period T begins on energisation. After timing, the output(s) R close(s). The second output can be either timed or instantaneous.

Function: 1 Output

### Function: 2 Outputs



2 timed outputs (R1/R2) or 1 timed output (R1) and 1 instantaneous output (R2 inst.)

# Product datasheet Technical Description

## **RE17LAMW**

### Legend

Relay de-energised

Relay energised

Output open

Output closed

C Control contact

G Gate

R Relay or solid state output

R1/R2 2 timed outputs

R2 inst. The second output is instantaneous if the right position is selected

T Timing periodTa Adjustable On-delayTr Adjustable Off-delay

U Supply

# Product datasheet Dimensions Drawings


## **RE17LAMW**

Width 17.5 mm

# Product datasheet Connections and Schema

## **RE17LAMW**

### Internal Wiring Diagram



# Product datasheet Connections and Schema

## **RE17LAMW**

### Wiring Diagram

