# Product datasheet Characteristics

# XS8C4A4PCP20

inductive sensor XS8 40x40x117 - PBT - Sn40 mm - 12..48VDC - terminals



#### Main

Pange of product	OpiCamas VC	
Range of product	OsiSense XS	
Series name	General purpose	
Sensor type	Inductive proximity sensor	
Device application	Mobile equipment	
Sensor name	XS8	
Sensor design	Form 40 x 40 x 117	
Size	117 mm	
Body type	Fixed	
Detector flush mounting acceptance	Non flush mountable	
Material	Plastic	
Enclosure material	PBT	
Type of output signal	Discrete	
Wiring technique	4-wire	
[Sn] nominal sensing distance	40 mm	
Discrete output function	1 NO + 1 NC	
Output circuit type	DC	
Discrete output type	PNP	
Electrical connection	Screw-clamp terminals, clamping capacity: 4 x 1.5 mm²	
[Us] rated supply voltage	1248 V DC with reverse polarity protection	
Switching capacity in mA	<= 200 mA with overload and short-circuit protection	
IP degree of protection	IP65 conforming to IEC 60529	
	IP67 conforming to IEC 60529	
	IP69K conforming to DIN 40050	

#### Complementary

o ompromontar y		
Safety level	SILCL 2 conforming to IEC 62061	. i
	PL = d conforming to EN/ISO 13849-1	F
	SIL 2 conforming to EN/IEC 61508	ā
Safety reliability data	ety reliability data SFF = 92 %	

DC = 75 % with appropriate safety controller
MTTFd = 1546 years
PFHd = 7.4E-8 1/h

Detection face	5 positions turret head	
Front material	PBT	
Operating zone	032 mm	
Differential travel	315% of Sr	
Repeat accuracy	<= 3% of Sr	
Cable entry number	1 tapped entry for M20 x 1.5 cable gland	
Status LED	1 LED green for supply on 1 LED yellow for output state	
Supply voltage limits	1058 V DC	
Switching frequency	<= 200 Hz	
Voltage drop	<= 2 V at closed state	
Current consumption	015 mA at no-load	
Delay first up	<= 7.5 ms	
Delay response	<= 1.4 ms	
Delay recovery	<= 2.5 ms	
Marking	CE	
Height	40 mm	
Length	40 mm	
Width	117 mm	
Product weight	0.244 kg	

### Environment

Environment		
Product certifications	E2	
	UL	
	TÜV	
	CCC	
	CSA	
Ambient air temperature for operation	n -2570 °C	
Ambient air temperature for storage	-4085 °C	
Vibration resistance	25 gn amplitude = +/- 2 mm (f = 1055 Hz) conforming to IEC 60068-2-6	
Shock resistance	50 gn for 11 ms conforming to EN 60068-2-27	

# Offer Sustainability

Green Premium product	
Compliant - since 1213 - Schneider Electric declaration of conformity	
Schneider Electric declaration of conformity	
Reference not containing SVHC above the threshold	
Reference not containing SVHC above the threshold	
Available	
Product environmental	
life instructions Need no specific recycling operations	
	Compliant - since 1213 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity  Reference not containing SVHC above the threshold  Reference not containing SVHC above the threshold  Available Product environmental


### Contractual warranty

Warranty period	18 months	

# **Product datasheet Dimensions Drawings**

# XS8C4A4PCP20

#### **Dimensions**




- 2 holes Ø 5,45 mm / Ø 0.21 in. (Tightening torque: < 1,5 Nm / &lt; 13.3 lb-in.)
   3 screws M3,5. (Tightening torque: &lt; 1,2 Nm / &lt; 10.6 lb-in.)
   2 elongated holes 5,4 x 7,4 mm / 0.21 x 0.29 in. (Tightening torque: &lt; 1,5 Nm / &lt; 13.3 lb-in.)

# Product datasheet Mounting and Clearance

# XS8C4A4PCP20

# Mounting


## **Head Positions**



# XS8C4A4PCP20


# Setting-up Precautions

### Side by Side




e (1) ≱60

#### Face to Face



e (2) ≵20

### Facing a Metal Object




e (3) ≱20

# Product datasheet Connections and Schema

# XS8C4A4PCP20

# Wiring Schemes


## 4-Wire DC



# XS8C4A4PCP20

## SIL 2 Wiring Scheme

## With Preventa XPSMF40 Safety PLC



SFF :(Safe Failure Fraction): 92,68 % DC : (Diagnosis Coverage): 75,8 %