

TMC2CONV01

cartridge M221 - conveying 1 serial line - I/O extension



Main

Range of product	Modicon M221
Product or component type	Serial line cartridge
Product compatibility	Modicon M221C
Product specific application	Conveying applications

Complementary

Integrated connection type	Non isolated serial link for screw terminal block (RS232) Non isolated serial link for screw terminal block (RS485)
Transmission rate	1.2...115.2 kbit/s (115.2 kbit/s by default), bus length = 15 m (RS485) 1.2...115.2 kbit/s (115.2 kbit/s by default), bus length = 3 m (RS232)
Communication port protocol	Modbus non isolated serial link for master/slave (RTU/ASCII or SoMachine-Network)
Insulation	Non-insulated between lines and internal logic
Height	41 mm
Depth	15 mm
Width	35 mm
Product weight	0.015 kg

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1415 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product environmental
Product end of life instructions	Available End of life manual