



### Main

|                           |                                                                                                                                                                                                                                                                                                                                                                                                  |
|---------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Range                     | Acti 9                                                                                                                                                                                                                                                                                                                                                                                           |
| Product name              | Disbo iC60                                                                                                                                                                                                                                                                                                                                                                                       |
| Product or component type | Miniature circuit-breaker                                                                                                                                                                                                                                                                                                                                                                        |
| Device short name         | IC60H                                                                                                                                                                                                                                                                                                                                                                                            |
| Poles description         | 3P                                                                                                                                                                                                                                                                                                                                                                                               |
| Number of protected poles | 3                                                                                                                                                                                                                                                                                                                                                                                                |
| [In] rated current        | 6 A                                                                                                                                                                                                                                                                                                                                                                                              |
| Network type              | AC                                                                                                                                                                                                                                                                                                                                                                                               |
| Trip unit technology      | Thermal-magnetic                                                                                                                                                                                                                                                                                                                                                                                 |
| Curve code                | C                                                                                                                                                                                                                                                                                                                                                                                                |
| Breaking capacity         | 10 kA Icu conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz<br>15 kA Icu conforming to EN/IEC 60947-2 - 380...415 V AC 50/60 Hz<br>30 kA Icu conforming to EN/IEC 60947-2 - 220...240 V AC 50/60 Hz<br>42 kA Icu conforming to EN/IEC 60947-2 - 12...133 V AC 50/60 Hz<br>20 kA Icu conforming to EN/IEC 60947-2 - 100...133 V DC<br>10000 A Icn conforming to EN/IEC 60898-1 - 415 V AC 50/60 Hz |
| Utilisation category      | Category A conforming to EN/IEC 60947-2                                                                                                                                                                                                                                                                                                                                                          |

### Complementary

|                                        |                                                                                                                                                                                                                                                                                                                                                                                                                                              |
|----------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Network frequency                      | 50/60 Hz                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| [Ue] rated operational voltage         | 440 V AC 50/60 Hz                                                                                                                                                                                                                                                                                                                                                                                                                            |
| Magnetic tripping limit                | 8 x In +/- 20 %                                                                                                                                                                                                                                                                                                                                                                                                                              |
| [Ics] rated service breaking capacity  | 15 kA 50 % x Icu conforming to EN/IEC 60947-2 - 220...240 V AC 50/60 Hz<br>7.5 kA 50 % x Icu conforming to EN/IEC 60947-2 - 380...415 V AC 50/60 Hz<br>21 kA 50 % x Icu conforming to EN/IEC 60947-2 - 12...133 V AC 50/60 Hz<br>20 kA 100 % x Icu conforming to EN/IEC 60947-2 - 100...133 V DC<br>10000 A 100 % x Icu conforming to EN/IEC 60898-1 - 415 V AC 50/60 Hz<br>5 kA 50 % x Icu conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz |
| Limitation class                       | 3 conforming to EN/IEC 60947-2                                                                                                                                                                                                                                                                                                                                                                                                               |
| [Ui] rated insulation voltage          | 500 V AC 50/60 Hz conforming to EN/IEC 60947-2                                                                                                                                                                                                                                                                                                                                                                                               |
| [Uimp] rated impulse withstand voltage | 6 kV conforming to EN/IEC 60947-2                                                                                                                                                                                                                                                                                                                                                                                                            |

|                            |                                                                                                                                                       |
|----------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Contact position indicator | Yes                                                                                                                                                   |
| Control type               | Toggle                                                                                                                                                |
| Local signalling           | Trip indicator                                                                                                                                        |
| Mounting mode              | Clip-on                                                                                                                                               |
| Mounting support           | Rail                                                                                                                                                  |
| 9 mm pitches               | 6                                                                                                                                                     |
| Height                     | 85 mm                                                                                                                                                 |
| Width                      | 54 mm                                                                                                                                                 |
| Depth                      | 78.5 mm                                                                                                                                               |
| Product weight             | 0.375 kg                                                                                                                                              |
| Colour                     | White                                                                                                                                                 |
| Mechanical durability      | 20000 cycles                                                                                                                                          |
| Electrical durability      | 10000 cycles                                                                                                                                          |
| Provision for padlocking   | Padlockable                                                                                                                                           |
| Connections - terminals    | Single terminal, top or bottom rigid wire(s) 1...25 mm <sup>2</sup> max<br>Single terminal, top or bottom flexible wire(s) 1...16 mm <sup>2</sup> max |
| Wire stripping length      | 14 mm top or bottom                                                                                                                                   |
| Tightening torque          | 2 N.m top or bottom                                                                                                                                   |
| Earth-leakage protection   | Separate block                                                                                                                                        |

## Environment

|                                       |                                  |
|---------------------------------------|----------------------------------|
| Standards                             | EN/IEC 60947-2<br>EN/IEC 60898-1 |
| IP degree of protection               | IP20 conforming to IEC 60529     |
| Pollution degree                      | 3 conforming to EN/IEC 60947-2   |
| Tropicalisation                       | 2 conforming to IEC 60068-1      |
| Relative humidity                     | 95 % ( 55 °C )                   |
| Ambient air temperature for operation | -35...70 °C                      |
| Ambient air temperature for storage   | -40...85 °C                      |

## Offer Sustainability

|                                  |                                                                                                                                       |
|----------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status         | Green Premium product                                                                                                                 |
| RoHS (date code: YYWW)           | Compliant - since 1310 - Schneider Electric declaration of conformity<br><a href="#">Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                |
| Product environmental profile    | Available                                                                                                                             |
| Product end of life instructions | Need no specific recycling operations                                                                                                 |