
Product datasheet Characteristics

NSYCVF300M230PF

ClimaSys forced vent. IP54, 300m3/h, 230V, with outlet grille and filter G2





Main

Range	ClimaSys	
Product name	ClimaSys CV	
Product or component type	Fan	
Type of ventilation filter	Standard	
Air flow	Free flow rate with standard filter: 350 m3/h at 60 Hz Free flow rate with standard filter: 300 m3/h at 50 Hz	
[Us] rated supply voltage	145253 V	
Input voltage	230 V 50/60 Hz	

Complementary

Main		
Range	ClimaSys	
Product name	ClimaSys CV	
Product or component type	Fan	
Type of ventilation filter	Standard	
Air flow	Free flow rate with standard filter : 350 m3/h at 60 Hz Free flow rate with standard filter : 300 m3/h at 50 Hz	
[Us] rated supply voltage	145253 V	
Input voltage	230 V 50/60 Hz	
Complementary		
Rated power in W	36 W 50 Hz 37 W 60 Hz	
[In] rated current	0.16 A 60 Hz 0.17 A 50 Hz	
Noise level	5556 dB	
Bearing type	Ball	
Height	External : 268 mm	
Width	External : 248 mm	
Depth	External : 116 mm	
Cut-out dimensions	223 x 223 mm	
Product weight	1.3 kg	
Material	Injected thermoplastic (ASA PC) for outlet grille	
Colour	Outlet grille : grey RAL 7035	
Ambient air temperature for operation	-1070 °C	
Ambient air temperature for storage	-4070 °C	
Maximum pressure	158 Pa flow rate 0 m³/h	
Connections - terminals	Faston connector	
IP degree of protection	IP54	
Apr. 00, 2047		

Device composition	1 outlet grille front	
	1 axial motor	
	2 protective grille on the front and rear surfaces	
	1 filter front of axial motor	
	1 cut-out template	
	1 power cord	
Condition of use	Flow rates depends on the work point, see ProClima software	
	Surrounding environment must be relatively clean	
	Outside temperature must be 5 °C lower than inside temperature	
	Filter must be cleaned and replaced regularly	
	Overfrequent filter replacement should be avoided	
Offer Sustainability		
Sustainable offer status	Not Green Premium product	
RoHS (date code: YYWW)		
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity	
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity	
RoHS (date code: YYWW) REACh		

Contractual warranty

Warranty period 18 months	