



Main


Range	ClimaSys
Product name	ClimaSys CV
Product or component type	Fan
Type of ventilation filter	Standard
Air flow	Free flow rate with standard filter : 39 m ³ /h at 60 Hz Free flow rate with standard filter : 38 m ³ /h at 50 Hz
[Us] rated supply voltage	150...250 V
Input voltage	230 V 50/60 Hz

Complementary

Rated power in W	4.5 W 50 Hz 4.8 W 60 Hz
[In] rated current	0.16 A 50 Hz 0.17 A 60 Hz
Noise level	40...41 dB
Bearing type	Ball
Height	External : 137 mm
Width	External : 117 mm
Depth	External : 49 mm
Cut-out dimensions	92 x 92 mm
Product weight	0.22 kg
Material	Injected thermoplastic (ASA PC) for outlet grille
Colour	Outlet grille : grey RAL 7035
Ambient air temperature for operation	-10...70 °C
Ambient air temperature for storage	-40...70 °C
Maximum pressure	29 Pa flow rate 0 m ³ /h
Connections - terminals	Cable
IP degree of protection	IP54

Device composition	<ul style="list-style-type: none"> 1 outlet grille front 1 axial motor 2 protective grille on the front and rear surfaces 1 filter front of axial motor 1 cut-out template
Condition of use	<ul style="list-style-type: none"> Outside temperature must be 5 °C lower than inside temperature Filter must be cleaned and replaced regularly Overfrequent filter replacement should be avoided Flow rates depends on the work point, see ProClima software Surrounding environment must be relatively clean
Installed device	-MUST NOT be connected to a power conversion module, an inverter or UPS type of power supply

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	<p>Compliant - since 0940 - Schneider Electric declaration of conformity</p> <p> Schneider Electric declaration of conformity</p>
REACH	<p>Reference not containing SVHC above the threshold</p> <p>Reference not containing SVHC above the threshold</p>

Contractual warranty

Warranty period	18 months
-----------------	-----------