



Main

Range	ClimaSys
Product name	ClimaSys CV
Product or component type	Fan
Range compatibility	Prisma P Prisma G
Type of ventilation filter	Standard
Air flow	Free flow rate with standard filter : 562 m ³ /h at 50 Hz Free flow rate with standard filter : 586 m ³ /h at 60 Hz
[Us] rated supply voltage	207...244 V
Input voltage	230 V 50/60 Hz

Complementary

Rated power in W	68 W 50 Hz 85 W 60 Hz
[In] rated current	0.52 A 50 Hz 0.37 A 60 Hz
Noise level	59 dB
Bearing type	Ball
Height	External : 336 mm
Width	External : 316 mm
Depth	External : 161 mm
Cut-out dimensions	291 x 291 mm
Product weight	3.2 kg
Material	Injected thermoplastic (ASA PC) for outlet grille
Colour	Outlet grille : grey RAL 7035
Ambient air temperature for operation	-15...60 °C
Ambient air temperature for storage	-40...70 °C
Maximum pressure	140 Pa flow rate 0 m ³ /h

Connections - terminals	Terminal block
IP degree of protection	IP54
Device composition	1 outlet grille front 1 axial motor 2 protective grille on the front and rear surfaces 1 filter front of axial motor 1 cut-out template
Condition of use	Overfrequent filter replacement should be avoided Filter must be cleaned and replaced regularly Outside temperature must be 5 °C lower than inside temperature Surrounding environment must be relatively clean Flow rates depends on the work point, see ProClima software

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------