# Product datasheet Characteristics

## XS630B1MAL5

inductive sensor XS6 M30 - L62mm - brass - Sn15mm - 24..240VAC/DC - cable 5m



#### Main

Mairi		
Range of product	OsiSense XS	
Series name	General purpose	
Sensor type	Inductive proximity sensor	
Device application	-	
Sensor name	XS6	
Sensor design	Cylindrical M30	
Size	62 mm	
Body type	Fixed	
Detector flush mounting acceptance	Flush mountable	
Material	Metal	
Type of output signal	Discrete	
Wiring technique	2-wire	
[Sn] nominal sensing distance	15 mm	
Discrete output function	1 NO	
Output circuit type	AC/DC	
Electrical connection	Cable	·
Cable length	5 m	
[Us] rated supply voltage	24240 V AC/DC (50/60 Hz)	
Switching capacity in mA	5200 mA DC 5300 mA AC	
IP degree of protection	IP68 double insulation conforming to IEC 60529 IP69K conforming to DIN 40050	

#### Complementary

P		<u> </u>
Thread type	M30 x 1.5	
Detection face	Frontal	. ic
Front material	PPS	
Enclosure material	Nickel plated brass	<u></u>

Operating zone	012 mm
Differential travel	115% of Sr
Cable composition	2 x 0.34 mm²
Wire insulation material	PvR
Status LED	1 LED (yellow) for output state
Supply voltage limits	20264 V AC/DC
Residual current	<= 0.8 mA, open state
Switching frequency	<= 25 Hz AC <= 500 Hz DC
Voltage drop	<= 5.5 V, closed state
Delay first up	<= 25 ms
Delay response	<= 0.5 ms
Delay recovery	<= 2 ms
Marking	CE
Threaded length	52 mm
Length	62 mm
Product weight	0.325 kg

### Environment

Product certifications	UL CSA	
Ambient air temperature for operation	-2570 °C	
Ambient air temperature for storage	-4085 °C	
Vibration resistance	25 gn, amplitude: +/- 2 mm (f = 1055 Hz) conforming to IEC 60068-2-6	
Shock resistance	50 gn (duration = 11 ms) conforming to IEC 60068-2-27	

## Offer Sustainability


Compliant - since 0813 - Schneider Electric declaration of conformity	
Schneider Electric declaration of conformity	
Reference not containing SVHC above the threshold	
Reference not containing SVHC above the threshold	
Available	
Product environmental	
Available	
🚰 End of life manual	
	Schneider Electric declaration of conformity  Reference not containing SVHC above the threshold  Reference not containing SVHC above the threshold  Available  Product environmental  Available

### Contractual warranty

Warranty period	18 months

# XS630B1MAL5

### **Dimensions**




(1) LED

# Product datasheet Mounting and Clearance

## XS630B1MAL5


## Minimum Mounting Distances

#### Side by side




e (1) \$0 mm/1.18 in.

Face to face



e (2) ≱80 mm/7.09 in. Facing a metal object



e (3) ≱5 mm/1.77 in.


# Product datasheet Connections and Schema

## XS630B1MAL5

## Wiring Schemes

## 2-Wire AC or DC

NO output



BU: Blue BN: Brown