Detailed Specifications & Technical Data



8772 Multi-Conductor - Audio, Control and Instrumentation Cable



For more Information please call

1-800-Belden1



General Description:

20 AWG stranded (7x28) tinned copper conductors, conductors cabled, polyethylene insulation, overall Beldfoil® shield (100% coverage), 20 AWG stranded tinned copper drain wire, PVC jacket.

Physical Characteristics (Overall)	
Conductor AWG:	
# Conductors AWG Stranding Conductor Material	
3 20 7x28 TC - Tinned Copper	
Total Number of Conductors:	3
Insulation Insulation Material:	
Insulation Material Wall Thickness (in.)	
PE - Polyethylene 0.017	
Outer Shield Outer Shield Material:	
Outer Shield Trade Name Type Outer Shield Material Beldfoil® (Z-Fold®) Tape Aluminum Foil-Polyester Ta	Coverage (%) ape 100
Outer Shield Drain Wire AWG:	
AWG Stranding Drain Wire Conductor Material 20 7x28 TC - Tinned Copper	
Outer Jacket Material:	
Outer Jacket Material Nom. Wall Thickness (in.) PVC - Polyvinyl Chloride .033	
2.000 Left Hand 6.000 Overall Cabling Color Code Chart: Number Color 1 Black 2 Red 3 Clear	
Overall Nominal Diameter:	0.218 in.
Mechanical Characteristics (Overall)	
Operating Temperature Range:	-20°C To +60°C
UL Temperature Rating:	60°C (UL AWM Style 2093)
Bulk Cable Weight:	29 lbs/1000 ft.
Max. Recommended Pulling Tension:	45 lbs.
Min. Bend Radius/Minor Axis:	2.250 in.
Applicable Specifications and Agency Complian Applicable Standards & Environmental Programs	ce (Overall)
NEC/(UL) Specification:	СМ
· · ·	
NEC Articles:	800
NEC Articles: CEC/C(UL) Specification:	800 CM

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

8772 Multi-Conductor - Audio, Control and Instrumentation Cable

EU CE Mark:	Yes			
EU Directive 2000/53/EC (ELV):	Yes			
EU Directive 2002/95/EC (RoHS):	Yes			
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004			
EU Directive 2002/96/EC (WEEE):	Yes			
EU Directive 2003/11/EC (BFR):	Yes			
CA Prop 65 (CJ for Wire & Cable):	Yes			
MII Order #39 (China RoHS):	Yes			
Flame Test				
UL Flame Test:	UL1685 UL Loading			
CSA Flame Test:	FT1			
Suitability				
Suitability - Indoor:	Yes			
Electrical Characteristics (Overall)				
Nom. Capacitance Conductor to Conductor:				
Capacitance (pF/ft) 27				
Nom. Capacitance Cond. to Other Conductor & Shield:				
Capacitance (pF/ft) 51				
Nom. Conductor DC Resistance:				
DCR @ 20°C (Ohm/1000 ft) 10.0				

Nominal Outer Shield DC Resistance: DCR @ 20°C (Ohm/1000 ft)

89 Max. Operating Voltage - UL: Voltage

300 V RMS

E

Max. Recommended Current:

Description Current 10C Temperature Rise 4 Amps per conductor @ 25°C ambient

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc	
8772 060U1000	1,000 FT	31.000 LB	CHROME		3 #20 PE FS PVC	
8772 060U500	500 FT	16.000 LB	CHROME		3 #20 PE FS PVC	
8772 0601000	1,000 FT	31.000 LB	CHROME	С	3 #20 PE FS PVC	
8772 060500	500 FT	16.000 LB	CHROME	С	3 #20 PE FS PVC	
8772 0605000	5,000 FT	155.000 LB	CHROME		3 #20 PE FS PVC	

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 08-05-2013

© 2017 Belden, Inc All Rights Reserved

All hough Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).