

HMIZRA1

Illuminated Switch-5 Function keys with multi-color LEDs backlit



Main

Range of product	Magelis HMIZ
Product or component type	Illuminated USB switch
Product compatibility	XBTGC XBTGT2... Magelis Panel PC HMISTO HMIGXO XBTGK XBTGT4... HMISCU XBTGT7... HMISTU XBTGT6... HMIGTO XBTGT5... Magelis Box PC HMIGTW
Device application	Industrial machines Food and beverage
Provided equipment	1 user manual 1 USB type B cable clamp 1 tightening wrench 1 anti-rotation tee 1 fixing nut 1 gasket 1 insert label 1 USB cable type A/B of 1 m

Complementary

Software designation	Vijeo Designer version >= V6.1 SP2
Connector type	USB type B
Control type	5 push-buttons with multi-colour backlit LED
Colour of cover	Front dark grey cover
[Us] rated supply voltage	5 V DC, connector type: USB 2.0

Supply voltage limits	4.75...5.25 V DC
Power consumption	2 W
Shock resistance	147 m/s ² (3 chocks in each direction X, Y and Z) conforming to IEC 61131-2
Electromagnetic compatibility	Electrostatic discharge immunity test - test level 8 kV (air discharge) conforming to IEC 61000-4-2 Electrical fast transient/burst immunity test - test level 2 kV (power ports) conforming to IEC 61000-4-4 Electrical fast transient/burst immunity test - test level 1 kV (signal ports) conforming to IEC 61000-4-4 Electrostatic discharge immunity test - test level 6 kV (contact discharge) conforming to IEC 61000-4-2
Mounting location	Flat surface
Quantity per set	1 piece
Height	54 mm
Width	122 mm
Depth	28 mm
Product weight	0.11 kg


Environment

Ambient air temperature for storage	-20...60 °C
Relative humidity	10...90 % at 0...55 °C (non-condensing)
Pollution degree	2
Environmental characteristic	Corrosive gas free
Operating altitude	<= 2000 m
Vibration resistance	3.5 mm (f=5...9 Hz) conforming to IEC 61131-2
IP degree of protection	IP65 front panel (in enclosure)
NEMA degree of protection	NEMA 13 for enclosed outdoor NEMA 4X for indoor installation
Standards	CSA C22.2 No 142 EMC 2004/108/EC WEEE directive 2002/96/EC ANSI/ISA 12.12.01 CSA C22.2 No 213 ROHS directive 2002/95/EC RoHS China SJ/T 11363-2006 EN 61000-6-2 UL 508 EN 61000-6-4
Product certifications	GOST UL/CUL listed CE C-Tick
Level or class	Class I Division 2 Groups A/B/C/D


Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 1535 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity


Dimensions



Dimensions with Cable



Mounting of Panel Cut-Out



Dimensions in mm

A	B	C	D
22.50 _{-0.30}	4 _{-0.20}	30 _{-0.20}	1.5...6

Dimensions in in.

A	B	C	D
0.88 _{-0.01}	0.15 _{-0.007}	1.18 _{-0.007}	0.06...0.23