



## Main

Range	TeSys
Product name	TeSys SK
Product or component type	Mini contactor
Device short name	LC1SK
Contactor application	Resistive load Motor control
Utilisation category	AC-3 AC-1
Poles description	2P
Pole contact composition	2 NO
[Ue] rated operational voltage	690 V AC 50/60 Hz for power circuit
[Ie] rated operational current	6 A at $\leq 440$ V AC AC-3 12 A ( $\leq 55$ °C) AC AC-1
Motor power kW	1.1 kW at 220...230 V AC 50/60 Hz 2.2 kW at 380...415 V AC 50/60 Hz 2.2 kW at 660...690 V AC 50/60 Hz
Control circuit type	AC 50/60 Hz
Control circuit voltage	240 V AC 50/60 Hz
[Ith] conventional free air thermal current	12 A at $\leq 55$ °C for power circuit
Irms rated making capacity	66 A at 690 V AC conforming to IEC 60947 66 A at 690 V AC conforming to NF C 63-110
Rated breaking capacity	52 A at $\leq 400$ V for power circuit conforming to NF C 63-110 52 A at $\leq 400$ V for power circuit conforming to IEC 60947
[Icw] rated short-time withstand current	50 A $\leq 55$ °C power circuit
Associated fuse rating	16 A gI at $\leq 440$ V for power circuit conforming to IEC 60947
Average impedance	4 mOhm at 50 Hz - Ith 12 A
[Ui] rated insulation voltage	690 V conforming to CSA C22.2 No 14 690 V conforming to BS 5424 690 V conforming to IEC 60947 690 V conforming to VDE 0110 group C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

690 V conforming to UL 508

Mounting support	Rail
Standards	BS 5424 NF C 63-110 IEC 60947 VDE 0660
Product certifications	UL CSA
Connections - terminals	Power circuit : connector 1 cable(s) 0.35...6 mm <sup>2</sup> - cable stiffness: flexible - with cable end Power circuit : connector 1 cable(s) 0.5...6 mm <sup>2</sup> - cable stiffness: flexible - without cable end Power circuit : connector 1 cable(s) 1.5...6 mm <sup>2</sup> - cable stiffness: solid Power circuit : connector 2 cable(s) 0.35...1.5 mm <sup>2</sup> - cable stiffness: flexible - with cable end Power circuit : connector 2 cable(s) 0.35...2.5 mm <sup>2</sup> - cable stiffness: flexible - without cable end Power circuit : connector 2 cable(s) 1.5...4 mm <sup>2</sup> - cable stiffness: solid
Tightening torque	0.8 N.m - on connector - with screwdriver pozidriv No 1
Operating time	6...8 ms coil de-energisation and NO opening 7...14 ms coil energisation and NO closing
Mechanical durability	10 Mcycles
Operating rate	1200 cyc/h

### Complementary

Control circuit voltage limits	0.2...0.75 U <sub>c</sub> at ≤ 50 °C drop-out 0.85...1.1 U <sub>c</sub> at ≤ 50 °C operational
Inrush power in VA	16 VA at 20 °C
Hold-in power consumption in VA	4.2 VA at 20 °C
Heat dissipation	1.4 W at 50/60 Hz

### Environment

IP degree of protection	IP2x conforming to VDE 0106
Protective treatment	TC conforming to IEC 60068 TC conforming to DIN 50015
Ambient air temperature for operation	-20...50 °C
Ambient air temperature for storage	-50...70 °C
Operating altitude	2000 m without derating in temperature
Height	56 mm
Width	27 mm
Depth	55.5 mm
Product weight	0.132 kg

### Contractual warranty

Warranty period	18 months
-----------------	-----------