



## SAFETY DATA SHEET BOSTIK 1782 TUBE

According to Regulation (EC) No 1907/2006

### SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

#### 1.1. Product identifier

Product name BOSTIK 1782 TUBE  
Product No. 06604, 30604527

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Adhesive.

#### 1.3. Details of the supplier of the safety data sheet

Supplier BOSTIK LIMITED  
COMMON ROAD  
STAFFORD  
STAFFORDSHIRE  
ST16 3EH  
+44 1785 272625  
sds.uk@bostik.com

#### 1.4. Emergency telephone number

+44 1785 272650 (24 Hours)

### SECTION 2: HAZARDS IDENTIFICATION

#### 2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical and Chemical Hazards Flam. Liq. 2 - H225  
Human health EUH066; Eye Irrit. 2 - H319; STOT SE 3 - H336  
Environment Not classified.

Classification (1999/45/EEC) Xi; R36. F; R11. R66, R67.

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

#### 2.2. Label elements

Label In Accordance With (EC) No. 1272/2008



Signal Word

Danger

Hazard Statements

H225 Highly flammable liquid and vapour.  
H319 Causes serious eye irritation.  
H336 May cause drowsiness or dizziness.

Precautionary Statements

P102 Keep out of reach of children.  
P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.  
P271 Use only outdoors or in a well-ventilated area.  
P280 Wear protective gloves/protective clothing/eye protection/face protection.  
P337+313 If eye irritation persists: Get medical advice/attention.

# BOSTIK 1782 TUBE

Supplementary Precautionary Statements	P501	Dispose of contents/container in accordance with local regulations.
	P233	Keep container tightly closed.
	P240	Ground/bond container and receiving equipment.
	P241	Use explosion-proof electrical equipment.
	P242	Use only non-sparking tools.
	P243	Take precautionary measures against static discharge.
	P261	Avoid breathing vapour/spray.
	P264	Wash contaminated skin thoroughly after handling.
	P370+378	In case of fire: Use foam, carbon dioxide, dry powder or water fog for extinction.
	P303+361+353	IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower.
	P304+340	IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.
	P305+351+338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
	P312	Call a POISON CENTER or doctor/physician if you feel unwell.
	P313	Get medical advice/attention.
	P403+233	Store in a well-ventilated place. Keep container tightly closed.
	P403+235	Store in a well-ventilated place. Keep cool.
	P405	Store locked up.
Supplemental label information		
	EUH066	Repeated exposure may cause skin dryness or cracking.

## 2.3. Other hazards

Vapours are heavier than air and can travel long distances to a source of ignition Pilot lights can ignite the vapour

## SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

### 3.2. Mixtures

ACETONE	60-100%
CAS-No.: 67-64-1	EC No.: 200-662-2
	Registration Number: 01-2119471330-49
Classification (EC 1272/2008)	Classification (67/548/EEC)
Flam. Liq. 2 - H225	F;R11
EUH066	Xi;R36
Eye Irrit. 2 - H319	R66
STOT SE 3 - H336	R67
BUTANONE	10-30%
CAS-No.: 78-93-3	EC No.: 201-159-0
	Registration Number: 01-2119457290-43
Classification (EC 1272/2008)	Classification (67/548/EEC)
Flam. Liq. 2 - H225	F;R11
EUH066	Xi;R36
Eye Irrit. 2 - H319	R66
STOT SE 3 - H336	R67

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

## SECTION 4: FIRST AID MEASURES

### 4.1. Description of first aid measures

#### Inhalation

Remove victim immediately from source of exposure. Move the exposed person to fresh air at once. Get medical attention.

# BOSTIK 1782 TUBE

## Ingestion

DO NOT induce vomiting. Get medical attention immediately.

## Skin contact

Promptly flush contaminated skin with water. Promptly remove clothing if soaked through and flush the skin with water. Wash skin with soap and water. Get medical attention if irritation persists after washing.

## Eye contact

Rinse the eye with water immediately. Continue to rinse for at least 15 minutes and get medical attention.

### 4.2. Most important symptoms and effects, both acute and delayed

#### Inhalation

No specific symptoms noted.

#### Ingestion

No specific symptoms noted.

#### Skin contact

No specific symptoms noted.

#### Eye contact

No specific symptoms noted.

### 4.3. Indication of any immediate medical attention and special treatment needed

## SECTION 5: FIREFIGHTING MEASURES

### 5.1. Extinguishing media

#### Extinguishing media

Fire can be extinguished using: Powder. Foam.

### 5.2. Special hazards arising from the substance or mixture

#### Hazardous combustion products

Not known.

#### Unusual Fire & Explosion Hazards

Generates massive smoke during fire. Vapours are heavier than air and may spread near ground to sources of ignition. HIGHLY FLAMMABLE! Risk of explosion in closed containers if pressure rises rapidly. Solvent vapours may form explosive mixtures with air. Specific hazards

Toxic gases/vapours/fumes of: Carbon dioxide (CO<sub>2</sub>). Carbon monoxide (CO).

### 5.3. Advice for firefighters

#### Special Fire Fighting Procedures

Not known.

#### Protective equipment for fire-fighters

Self contained breathing apparatus and full protective clothing must be worn in case of fire.

## SECTION 6: ACCIDENTAL RELEASE MEASURES

### 6.1. Personal precautions, protective equipment and emergency procedures

Avoid contact with skin and eyes. Provide adequate ventilation. Wear protective clothing as described in Section 8 of this safety data sheet.

### 6.2. Environmental precautions

Prevent entry into drains. Avoid discharge into water courses or onto the ground.

### 6.3. Methods and material for containment and cleaning up

Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Runoff or release to sewer, waterway or ground is forbidden. Absorb with sand or other inert absorbent. Collect with absorbent, non-combustible material into suitable containers. Containers with collected spillage must be properly labelled with correct contents and hazard symbol.

### 6.4. Reference to other sections

Wear protective clothing as described in Section 8 of this safety data sheet.

## SECTION 7: HANDLING AND STORAGE

### 7.1. Precautions for safe handling

## BOSTIK 1782 TUBE

Keep away from heat, sparks and open flame. Avoid spilling, skin and eye contact. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

### 7.2. Conditions for safe storage, including any incompatibilities

Flammable/combustible - Keep away from oxidisers, heat and flames. Ground container and transfer equipment to eliminate static electric sparks. Store at moderate temperatures in dry, well ventilated area.

Storage Class

Flammable liquid storage.

### 7.3. Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

## SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

### 8.1. Control parameters

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
ACETONE	WEL	500 ppm	1210 mg/m <sup>3</sup>	1500 ppm	3620 mg/m <sup>3</sup>	
BUTANONE	WEL	200 ppm(Sk)	600 mg/m <sup>3</sup> (Sk)	300 ppm(Sk)	899 mg/m <sup>3</sup> (Sk)	

WEL = Workplace Exposure Limit.

Ingredient Comments

WEL = Workplace Exposure Limits

### 8.2. Exposure controls

Protective equipment



Engineering measures

Explosion-proof general and local exhaust ventilation.

Respiratory equipment

Respiratory protection must be used if air contamination exceeds acceptable level. Wear mask supplied with: Gas cartridge suitable for organic substances.

Hand protection

Protective gloves must be used if there is a risk of direct contact or splash. Use protective gloves made of: Nitrile. Use thin cotton gloves inside the rubber gloves if allergy risk.

Eye protection

Wear splash-proof eye goggles to prevent any possibility of eye contact.

Other Protection

Wear appropriate clothing to prevent repeated or prolonged skin contact.

Hygiene measures

DO NOT SMOKE IN WORK AREA! Wash promptly if skin becomes contaminated. Wash hands at the end of each work shift and before eating, smoking and using the toilet. Use appropriate skin cream to prevent drying of skin.

## SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

### 9.1. Information on basic physical and chemical properties

Appearance	Liquid
Colour	Colourless.
Odour	Ketonic.
Solubility	Miscible with water
Relative density	0.86 @ 25 °c
Flash point (°C)	- 18 CC (Closed cup).
Flammability Limit - Lower(%)	2.0
Flammability Limit - Upper(%)	13.3

# BOSTIK 1782 TUBE

## 9.2. Other information

### SECTION 10: STABILITY AND REACTIVITY

#### 10.1. Reactivity

No data available

#### 10.2. Chemical stability

Avoid Heat, sparks, flames.

#### 10.3. Possibility of hazardous reactions

Not available.

Hazardous Polymerisation

Unknown.

#### 10.4. Conditions to avoid

Not known.

#### 10.5. Incompatible materials

Materials To Avoid

Strong oxidising substances.

#### 10.6. Hazardous decomposition products

Fire or high temperatures create: Toxic gases/vapours/fumes of: Carbon dioxide (CO<sub>2</sub>). Carbon monoxide (CO).

### SECTION 11: TOXICOLOGICAL INFORMATION

#### 11.1. Information on toxicological effects

Inhalation

Drowsiness, dizziness, disorientation, vertigo. Gas or vapour may irritate respiratory system.

Ingestion

Pneumonia may be the result if vomited material containing solvents reaches the lungs.

Skin contact

Prolonged contact may cause dryness of the skin. May cause skin irritation/eczema.

Eye contact

Irritating to eyes. Irritation, burning, lachrymation, blurred vision after liquid splash.

Health Warnings

Defats the skin. Prolonged or repeated exposure may cause severe irritation.

Medical Considerations

Skin disorders and allergies.

### SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicity

Not regarded as dangerous for the environment. However, contamination of the aquatic or terrestrial environments should be avoided

#### 12.1. Toxicity

No data available

#### 12.2. Persistence and degradability

Degradability

There are no data on the degradability of this product.

#### 12.3. Bioaccumulative potential

# BOSTIK 1782 TUBE

Bioaccumulative potential

No data available on bioaccumulation.

## 12.4. Mobility in soil

Mobility:

Semi-mobile.

## 12.5. Results of PBT and vPvB assessment

No data available

## 12.6. Other adverse effects

Not available.

## SECTION 13: DISPOSAL CONSIDERATIONS

General information

Waste is classified as hazardous waste. Disposal to licensed waste disposal site in accordance with the local Waste Disposal Authority.

### 13.1. Waste treatment methods

Dispose of waste and residues in accordance with local authority requirements. Do not allow runoff to sewer, waterway or ground.

Recover and reclaim or recycle, if practical.

Waste Class

Classified as Special Waste. Not permitted for landfill in liquid state.

## SECTION 14: TRANSPORT INFORMATION

### 14.1. UN number

UN No. (ADR/RID/ADN) 1133

UN No. (IMDG) 1133

UN No. (ICAO) 1133

### 14.2. UN proper shipping name

Proper Shipping Name ADHESIVES

### 14.3. Transport hazard class(es)

ADR/RID/ADN Class 3

ADR/RID/ADN Class Class 3: Flammable liquids.

ADR Label No. 3

IMDG Class 3

ICAO Class/Division 3

Transport Labels



### 14.4. Packing group

ADR/RID/ADN Packing group III

IMDG Packing group III

ICAO Packing group III

### 14.5. Environmental hazards

# BOSTIK 1782 TUBE

Environmentally Hazardous Substance/Marine Pollutant  
No.

## 14.6. Special precautions for user

EMS	F-E, S-D
Emergency Action Code	•3YE
Hazard No. (ADR)	33
Tunnel Restriction Code	(D/E)

## 14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

### SECTION 15: REGULATORY INFORMATION

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

##### Statutory Instruments

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (S.I 2009 No. 716). Control of Substances Hazardous to Health.

##### Approved Code Of Practice

Classification and Labelling of Substances and Preparations Dangerous for Supply.

##### Guidance Notes

Workplace Exposure Limits EH40. CHIP for everyone HSG(108). Introduction to Local Exhaust Ventilation HS(G)37.

##### EU Legislation

Dangerous Substance Directive 67/548/EEC. Dangerous Preparations Directive 1999/45/EC. Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

#### 15.2. Chemical Safety Assessment

### SECTION 16: OTHER INFORMATION

##### General information

This product should be used as directed by Bostik Ltd. For further information consult the product data sheet or contact Technical Services.

##### Information Sources

This safety data sheet was compiled using current safety information supplied by distributor of raw materials.

##### Revision Comments

NOTE: Lines within the margin indicate significant changes from the previous revision. This safety data sheet supersedes all previous issues and users are cautioned to ensure that it is current. Destroy all previous data sheets and if in doubt contact Bostik Limited.

Issued By	Approved LJ
Revision Date	January 2014
Revision	14
Date	December 2002

##### Risk Phrases In Full

R11	Highly flammable
R36	Irritating to eyes.
R66	Repeated exposure may cause skin dryness or cracking.
R67	Vapours may cause drowsiness and dizziness.

##### Hazard Statements In Full

EUH066	Repeated exposure may cause skin dryness or cracking.
H225	Highly flammable liquid and vapour.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.