

For more Information  
please call

1-800-Belden1



## General Description:

14 AWG solid .064" bare copper conductor, gas-injected foam HDPE insulation, bare copper double shields (95% and 80% coverage), polyethylene jacket.

## Physical Characteristics (Overall)

### Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	14	Solid	BC - Bare Copper	.064

Total Number of Conductors: 1

### Insulation

Insulation Material:

Insulation Material	Dia. (in.)
Gas-injected FHDPE - Foam High Density Polyethylene	.285

### Inner Shield

Inner Shield Material:

Type	Inner Shield Material	Coverage (%)
Braid	BC - Bare Copper	95

### Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Dia. (in.)
PE - Polyethylene	.365

### Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	BC - Bare Copper	80

### Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PE - Polyethylene

### Overall Cable

Overall Nominal Diameter: 0.475 in.

## Mechanical Characteristics (Overall)

Operating Temperature Range: -55°C To +80°C

Non-UL Temperature Rating: 80°C

Bulk Cable Weight: 112 lbs/1000 ft.

Max. Recommended Pulling Tension: 170 lbs.

Min. Bend Radius/Minor Axis: 5 in.

## Applicable Specifications and Agency Compliance (Overall)

### Applicable Standards & Environmental Programs

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: No

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
RG Type:	11/U

**Suitability**

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Aerial:	Yes, when supported by a messenger wire
Suitability - Burial:	Yes

**Plenum/Non-Plenum**

Plenum (Y/N):	No
---------------	----

**Electrical Characteristics (Overall)**

**Nom. Characteristic Impedance:**

**Impedance (Ohm)**  
75

**Nom. Inductance:**

**Inductance (µH/ft)**  
0.097

**Nom. Capacitance Conductor to Shield:**

**Capacitance (pF/ft)**  
16.1

**Nominal Velocity of Propagation:**

**VP (%)**  
84

**Nominal Delay:**

**Delay (ns/ft)**  
1.20

**Nom. Conductor DC Resistance:**

**DCR @ 20°C (Ohm/1000 ft)**  
2.600

**Nom. Inner Shield DC Resistance:**

**DCR @ 20°C (Ohm/1000 ft)**  
1.700

**Nominal Outer Shield DC Resistance:**

**DCR @ 20°C (Ohm/1000 ft)**  
1.500

**Nom. Attenuation:**

Freq. (MHz)	Attenuation (dB/100 ft.)
1.000	0.140
3.600	0.300
10.000	0.400
71.500	1.100
135.000	1.600
270.000	2.300
360.000	2.600
540.000	3.300
720.000	3.800
750.000	4.000
1000.000	4.600
1500.000	5.900
2250.000	7.400
3000.000	9.000
4500.000	12.500

**Max. Operating Voltage - Non-UL:**

**Voltage**  
300 V RMS

**Minimum Return Loss:**

Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
5.000	850.000	21.000
850.000	4500.000	15.000

### Sweep Test

Sweep Testing: 100&#37; Sweep tested 5 MHz to 4.5 GHz.

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8233 0101000	1,000 FT	119.000 LB	BLACK	C	RG-11/U TYPE TRIAX
8233 0102000	2,000 FT	240.000 LB	BLACK	C	RG-11/U TYPE TRIAX
8233 010500	500 FT	63.000 LB	BLACK	C	RG-11/U TYPE TRIAX

**Notes:**

C = CRATE REEL PUT-UP.

Revision Number: 3    Revision Date: 06-26-2013

© 2017 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.