

EMERGENCY SERVICE ANTENNA MULTIFUNCTION MIMO ANTENNA

The Emergency Service antenna has a compact OEM style shark fin housing that contains 2x2 MiMo antenna function for 4G/3G/2G and an active antenna for GPS/GLONASS/Galileo/Beidou with 26 dB gain LNA. In addition, there is an integral stud mount for an external antenna whip that can support a range of VHF, UHF or 700/800MHz antennas. A blanking cover is supplied for when an external whip is not required. A further version of Emergency Service antenna is available that adds 2x2 MiMo antenna function for 2.4/5.8GHz WiFi.

The antenna's shark fin style design provides multiple antenna functions while remaining discreet and is suitable for public safety (overt/covert), industrial and transport applications where a cost effective, efficient and robust antenna is essential. Requiring only a single hole mounting, the Emergency Service antenna reduces vehicle damage, installation time & cost and visual impact whilst protecting a vehicle's resale value.







Multifunction MiMo Antenna

Technical Information

Technical Information		Part Numbers	
		1-2823602-2	1-2823602-1
Electrical Data			
Frequency Range (MHz)	Element 1	2562-1612	
	Element 2 & 3	698-960, 1710-2170, 2500-3800	
	Elements 4 & 5	- 2300-2500 & 4900-6000	
	Whip	Dependent on selected whip	
Operational Bands	Element 1	GPS/GNSS/Galileo/Beidou	
	Elements 2 & 3	4G/3G/2G	
	Elements 4 & 5	-	2.4GHz WLAN/Public Safety 4.9GHz/5.8GHz WiFi
	Whip	Dependent on selected whip	
Peak gain: Isotropic*	Elements 2 & 3	2dBi (698-960MHz)	5dBi (1710-3800MHz)
	Elements 3 & 4	-	4dBi (2.4GHz), 6dBi (5.8GHz)
Isolation (with 5m (16') CS29	Cellular	>12dB	
	WiFi	>20dB	
Typical Efficiency* w/o cable loss	Elements 2 & 3	>50%	
Correlation Co-efficient	Elements 2 & 3	<0.2	
Polarisation		Vertical	
Pattern		Omni-directional	
Impedance		50Ω	
Max Input Power		Internal elements 25W/main whip 60W	
GPS/GNSS Data			
Frequency Range (MHz)		1562-1612MHz	
VSWR		<2:1 <u>+</u> 4MHz	
LNA Gain		26dB	
Polarisation		Right Hand Circular	
Operating Voltage		3-5VDC (Fed via Coax)	
Current		Typical <20mA	
Mechanical Data			
Dimensions (mm)	Height (excluding whip)	50 (2.2")	
	Length	17 (6.77")	
	Width	60 (2.4")	
Operating Temp (°C)		-40 to +80 (-40°F to 176°F)	
Material		ASA, EPDM, Aluminium Alloy	
Colour		Black	
Typical Weight (g)		240	260
Cable Data			
Cable Type - All Feeds		RG174 (UN ECE 118.01 Compliant)	
Dimensions (mm)	Diameter	2.8 (0.11")	
	Length	300 mm (12")	
Termination	Whip	FME plug	
	GPS/GNSS	FME socket	
	2 x 4G/3G/2G	2 x SMA plug	
	2 x WiFi	-	2 x SMA socket



EMERGENCY SERVICE ANTENNA

Multifuncational MiMo Antenna



*Isolation measured with no whip and 5m (16') of CS29 cable Red Plot = 600x600mm (2' X2') ground plane Green Plot = no ground plane



EMERGENCY SERVICE ANTENNA

Multifunctional MiMo Antenna





EMERGENCY SERVICE ANTENNA

Multifunctional MiMo Antenna

3D Radiation Patterns - WiFi Elements 4&5



*3D radiation patterns simulated in CST Microwave Studio on a 600x600mm (2' X2') ground plane with both elements fed together.



Typical Total Efficiency - Cellular Elements 2&3*

180

* Efficient simulated in free space with no whip and no ground plane and no cable.

Typical Correlation Co-efficient - Cellular Elements 2&3*



*Correlation co-efficient simulated in free space with no whip, no additional cable and no ground plane

* 3D radiation patterns simulated in CST Microwave Studio on a 600x600mm (2'x2') ground plane with both elements fed together.

