


## 1227A1 Multi-Conductor - Category 3 Nonbonded-Pair Cable



For more Information  
please call

1-800-Belden1



### General Description:

CAT3 (16MHz), 2-Pair, U/UTP-Unshielded, Riser-CMR, Premise Horizontal Cable, 24 AWG solid bare copper conductors, Polyolefin insulation, PVC jacket

### Physical Characteristics (Overall)

#### Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
2	24	Solid	BC - Bare Copper

Total Number of Conductors: 4

#### Insulation

Insulation Material:

Insulation Material
PP - Polypropylene

#### Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

#### Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Diameter:

Nom. Dia. (in.)
0.173

#### Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange

### Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +80°C
UL Temperature Rating:	75°C
Bulk Cable Weight:	13 lbs/1000 ft.
Max. Recommended Pulling Tension:	15 lbs.
Min. Bend Radius/Minor Axis:	1 in.
Min. Bend/Installation:	1.700 in.

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMR, UL444
EU Directive 2011/65/EU (ROHS II):	Yes
IEEE Specification:	802.3 10BaseT, 100BaseT4
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes

## 1227A1 Multi-Conductor - Category 3 Nonbonded-Pair Cable

EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	NEMA WC-63 Category 3

### Flame Test

UL Flame Test:	UL1666 Riser
CSA Flame Test:	FT4

### Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Sunlight Resistance:	Yes

### Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	1243A2

## Electrical Characteristics (Overall)

### Nom. Mutual Capacitance:

#### Capacitance (pF/ft)

15

Maximum Capacitance Unbalance (pF/100 m): 330

### Nominal Velocity of Propagation:

#### VP (%)

70

### Nominal Delay:

#### Delay (ns/ft)

1.5

### Nom. Conductor DC Resistance:

#### DCR @ 20°C (Ohm/1000 ft)

28.0

### Maximum Conductor DC Resistance:

#### DCR @ 20°C (Ohm/100 m)

9.38

### Max. Operating Voltage - UL:

#### Voltage

300 V RMS

### Maximum DCR Unbalanced:

#### DCR Unbalance @ 20°C (%)

5

## Electrical Characteristics-Premise (Overall)

### Premise Cable Electricals:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. SRL (dB)	Fitted Imp. (Ohms)
1	2.56	41.0	No Spec	12.0	100 ± 15%
4	5.58	32.0	No Spec	12.0	100 ± 15%
8	8.50	27.0	No Spec	12.0	100 ± 15%
10	9.71	26.0	No Spec	12.0	100 ± 15%
16	13.10	23.0	No Spec	9.96	100 ± 15%

## Notes (Overall)

Notes: Jacket sequentially marked at 2 ft. intervals. Third party verified to TIA/EIA-568-B.2, Category 3

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1227A1 Q5HU1000	1,000 FT	14.000 LB	WHITE, NEUTRAL		CAT3 2PR U/UTP CMR BOX
1227A1 008U1000	1,000 FT	14.000 LB	GRAY		CAT3 2PR U/UTP CMR BOX

## 1227A1 Multi-Conductor - Category 3 Nonbonded-Pair Cable

Revision Number: 2    Revision Date: 08-14-2013

© 2017 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).