# Product datasheet Characteristics

# LC1D18F7

TeSys D contactor - 3P(3 NO) - AC-3 - <= 440 V 18 A - 110 V AC coil



#### Main

Main	
Range of product	TeSys D
Range	TeSys
Product name	TeSys D
Product or component type	Contactor
Device short name	LC1D
Contactor application	Resistive load Motor control
Utilisation category	AC-4 AC-3 AC-1
Poles description	3P
Pole contact composition	3 NO
[Ue] rated operational voltage	<= 300 V DC for power circuit <= 690 V AC 25400 Hz for power circuit
[le] rated operational current	18 A (<= 60 °C) at <= 440 V AC AC-3 for power circuit 32 A (<= 60 °C) at <= 440 V AC AC-1 for power circuit
Motor power kW	10 kW at 500 V AC 50/60 Hz AC-3 10 kW at 660690 V AC 50/60 Hz AC-3 4 kW at 220230 V AC 50/60 Hz AC-3 7.5 kW at 380400 V AC 50/60 Hz AC-3 9 kW at 415440 V AC 50/60 Hz AC-3 4 kW at 400 V AC 50/60 Hz AC-4
Motor power hp	1 hp at 115 V AC 50/60 Hz for 1 phase motors 3 hp at 230/240 V AC 50/60 Hz for 1 phase motors 5 hp at 200/208 V AC 50/60 Hz for 3 phases motors 5 hp at 230/240 V AC 50/60 Hz for 3 phases motors 10 hp at 460/480 V AC 50/60 Hz for 3 phases motors 15 hp at 575/600 V AC 50/60 Hz for 3 phases motors
Control circuit type	AC 50/60 Hz
Control circuit voltage	110 V AC 50/60 Hz
Auxiliary contact composition	1 NO + 1 NC
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947

Overvoltage category	
[Ith] conventional free air thermal	32 A at <= 60 °C for power circuit
current	10 A at <= 60 °C for signalling circuit
Irms rated making capacity	300 A at 440 V for power circuit conforming to IEC 60947 140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1
Rated breaking capacity	300 A at 440 V for power circuit conforming to IEC 60947
[Icw] rated short-time withstand current	145 A <= 40 °C 10 s power circuit 240 A <= 40 °C 1 s power circuit 40 A <= 40 °C 10 min power circuit 84 A <= 40 °C 1 min power circuit 100 A 1 s signalling circuit 120 A 500 ms signalling circuit 140 A 100 ms signalling circuit
Associated fuse rating	35 A gG at <= 690 V coordination type 2 for power circuit 50 A gG at <= 690 V coordination type 1 for power circuit 10 A gG for signalling circuit conforming to IEC 60947-5-1
Average impedance	2.5 mOhm at 50 Hz - Ith 32 A for power circuit
[Ui] rated insulation voltage	600 V for power circuit certifications CSA 600 V for power circuit certifications UL 690 V for power circuit conforming to IEC 60947-4-1 690 V for signalling circuit conforming to IEC 60947-1 600 V for signalling circuit certifications CSA 600 V for signalling circuit certifications UL
Electrical durability	1.65 Mcycles 18 A AC-3 at Ue <= 440 V 1 Mcycles 32 A AC-1 at Ue <= 440 V
Power dissipation per pole	0.8 W AC-3 2.5 W AC-1
Protective cover	With
Mounting support	Rail Plate
Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508
Product certifications	GOST UL LROS DNV CCC RINA CSA BV GL
Connections - terminals	Control circuit : screw clamp terminals 2 cable(s) 12.5 mm² - cable stiffness: flexible - with cable end
	Power circuit: screw clamp terminals 1 cable(s) 16 mm² - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm² - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 2 cable(s) 14 mm² - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm² - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm² - cable stiffness: solid - without cable end Control circuit: screw clamp terminals 2 cable(s) 14 mm² - cable stiffness: solid - without cable end Power circuit: screw clamp terminals 1 cable(s) 1.56 mm² - cable stiffness: flexible - without cable end Power circuit: screw clamp terminals 2 cable(s) 1.56 mm² - cable stiffness: flexible - without cable end Power circuit: screw clamp terminals 2 cable(s) 14 mm² - cable stiffness: flexible - without cable end Power circuit: screw clamp terminals 1 cable(s) 1.56 mm² - cable stiffness: solid - without cable end Power circuit: screw clamp terminals 2 cable(s) 1.56 mm² - cable stiffness: solid - without cable end Power circuit: screw clamp terminals 2 cable(s) 1.56 mm² - cable stiffness: solid - without cable end Power circuit: screw clamp terminals 2 cable(s) 1.56 mm² - cable stiffness: solid - without cable end
Tightening torque	Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2

Operating time	419 ms opening 1222 ms closing
Safety reliability level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical durability	15 Mcycles
Operating rate	3600 cyc/h at <= 60 °C

## Complementary

Coil technology	Without built-in suppressor module	
Control circuit voltage limits	0.30.6 Uc drop-out at 60 °C, AC 50/60 Hz 0.81.1 Uc operational at 60 °C, AC 50 Hz 0.851.1 Uc operational at 60 °C, AC 60 Hz	
Inrush power in VA	70 VA at 20 °C (cos φ 0.75) 60 Hz 70 VA at 20 °C (cos φ 0.75) 50 Hz	
Hold-in power consumption in VA	7.5 VA at 20 °C (cos φ 0.3) 60 Hz 7 VA at 20 °C (cos φ 0.3) 50 Hz	
Heat dissipation	23 W at 50/60 Hz	
Auxiliary contacts type	Type mechanically linked (1 NO + 1 NC) conforming to IEC 60947-5-1  Type mirror contact (1 NC) conforming to IEC 60947-4-1	
Signalling circuit frequency	25400 Hz	
Minimum switching current	5 mA for signalling circuit	
Minimum switching voltage	17 V for signalling circuit	
Non-overlap time	1.5 ms on energisation between NC and NO contact 1.5 ms on de-energisation between NC and NO contact	
Insulation resistance	> 10 MOhm for signalling circuit	
Motor power range AC-3	711 kW 380440 V 3 phases 711 kW 480500 V 3 phases 46 kW 200240 V 3 phases	
Motor starter type	Direct on-line contactor	
Contactor coil voltage	110 V AC	

### Environment

IP2x front face conforming to IEC 60529
TH conforming to IEC 60068-2-30
3
-2060 °C
-6080 °C
-4070 °C at Uc
3000 m without derating in temperature
850 °C conforming to IEC 60695-2-1
V1 conforming to UL 94
Vibrations contactor open 2 Gn, 5300 Hz Vibrations contactor closed 4 Gn, 5300 Hz Shocks contactor open 10 Gn for 11 ms Shocks contactor closed 15 Gn for 11 ms
77 mm
45 mm
86 mm
0.33 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0627 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACh	Reference not containing SVHC above the threshold

Reference	not cor	taining	SVHC	ahove	the t	hrachold
Reference	TIOL COL	namma	SVEL	anove	ine i	nresnoid

Available  Product environmental
Available  End of life manual


#### Contractual warranty

Warranty period	18 months

# Product datasheet **Dimensions Drawings**

# LC1D18F7

#### **Dimensions**




- (1) (2)
- Including LAD 4BB Minimum electrical clearance

LC1		D09D18	D093D123	D099D129
b	without add-on blocks	77	99	80
b1	with LAD 4BB	94	107	95.5
with LA4 D	<b>°</b> <sup>2</sup> 10 <sup>(1)</sup>	123 <sup>(1)</sup>	111.5 <sup>(1)</sup>	
with LA4 D	F1 (ATT)	132 <sup>(1)</sup>	120.5 <sup>(1)</sup>	
with LA4 D	W28 <sup>11</sup>	139 <sup>(1)</sup>	127.5 <sup>(1)</sup>	
С	without cover or add-on blocks	84	84	84
with cover,	ზ6hout add-on blocks	86	86	
c1	with LAD N or C (2 or 4 contacts)	117	117	117
c2	with LA6 DK10, LAD 6K10	129	129	129
с3	with LAD T, R, S	137	137	137
with LAD T	, 13,1S and sealing cover	141	141	
(1)	Including LAD 4BB.	•		

# Product datasheet Connections and Schema

# LC1D18F7

## Wiring



## LC1D18F7

--- File: MPC-LC1D18F7-BOM.xml , Range ID: 664, Reference ID: LC1D18F7 -->

#### Our Proposal - Type 1 : Circuit Breaker + Contactor for Motor Power 7,5 kW and 415 VAC

## <!-- DataBOM 2 Template BEGIN -->

Motor Power (kW)	lcu (kA)	Breaker	Contactor
7.5	15		
		GV2ME20	LC1D18F7

Non contractual pictures. Type 1 coordination requires that in a short-circuit condition, the contactor or starter must not present any danger to personnel or installations and must not be able to resume operation without repair or the replacement of parts.

<!-- DataBOM 2 Template END --> <!-- No Variants -->