Product datasheet Characteristics

XALD324

dark grey station - white flush/red flush/black flush pushbuttons \emptyset 22



Main

Main		
Range of product	Harmony XALD	
Product or component type	Complete control station	
Device short name	XALD	
Product destination	For XB5 Ø 22 mm control and signalling units	
Control station application	Three functions	
Colour of base of enclosure	Light grey RAL 7035	
Colour of cover	Dark grey RAL 7016	
Material	Polycarbonate	
Operator profile	3 flush push-buttons	
Operators description	White "up arrow" 1 NO - red "O" 1 NC - black "down arrow" 1 NO	
Control station composition	1 flush push-button red 1 NC O marking 1 flush push-button white 1 NO black up arrow marking 1 flush push-button black 1 NO white down arrow marking	
Marking location	Marking on push-button	
Contacts operation	Slow-break	

Complementary

Cable entry	2 knock-outs for cable entry, clamping capacity: <= 14 mm 2 knock-outs for Pg 13 cable gland and ISO M20, clamping capacity: <= 12 mm	
Product weight	0.298 kg	
Resistance to high pressure washer	7000000 Pa at 55 °C, distance: 0.1 m	
Colour of marking	White marking when green, red or black caps Black marking when white caps	
Positive opening	With conforming to EN/IEC 60947-5-1 : appendix K	
Operating travel	1.5 mm (NC changing electrical state) 2.6 mm (NO changing electrical state) 4.3 mm (total travel)	
Operating force	3.5 N (NC changing electrical state) 3.8 N (NO changing electrical state)	

Mechanical durability	10000000 cycles	
Connections - terminals	Screw clamp terminals : <= 2 x 1.5 mm² with cable end conforming to EN/IEC 60947-1 Screw clamp terminals : >= 1 x 0.22 mm² without cable end conforming to EN/IEC 60947-1	
Tightening torque	0.81.2 N.m conforming to EN/IEC 60947-1	
Shape of screw head	Cross, Philips no 1 Cross, pozidriv No 1 Slotted, flat Ø 4 mm Slotted, flat Ø 5.5 mm	
Contacts material	Silver alloy (Ag/Ni)	
Short circuit protection	10 A by gG cartridge fuse conforming to EN/IEC 60947-5-1	
[Ith] conventional free air thermal current	10 A conforming to EN/IEC 60947-5-1	
[Ui] rated insulation voltage	600 V (degree of pollution: 3) conforming to EN/IEC 60947-1	
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-1	
[le] rated operational current	AC-15, A600: Ue = 120 V Ie = 6 A conforming to EN/IEC 60947-5-1 AC-15, A600: Ue = 240 V Ie = 3 A conforming to EN/IEC 60947-5-1 AC-15, A600: Ue = 600 V Ie = 1.2 A conforming to EN/IEC 60947-5-1 DC-13, Q600: Ue = 125 V Ie = 0.55 A conforming to EN/IEC 60947-5-1 DC-13, Q600: Ue = 250 V Ie = 0.27 A conforming to EN/IEC 60947-5-1 DC-13, Q600: Ue = 600 V Ie = 0.1 A conforming to EN/IEC 60947-5-1	
Electrical durability	1000000 cycles AC-15, 2 A at 230 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1 appendix C 1000000 cycles AC-15, 3 A at 120 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1 appendix C 1000000 cycles AC-15, 4 A at 24 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C 1000000 cycles DC-13, 0.2 A at 110 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1 appendix C 1000000 cycles DC-13, 0.5 A at 24 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1 appendix C	
Electrical reliability IEC 60947-5-4	Λ < 10exp(-6) at 5 V, 1 mA conforming to EN/IEC 60947-5-4 Λ < 10exp(-8) at 17 V, 5 mA conforming to EN/IEC 60947-5-4	


Environment

Protective treatment	TH	
Ambient air temperature for storage	-4070 °C	
Ambient air temperature for operation	-4070 °C	
Class of protection against electric shock	Class II conforming to IEC 60536	
IP degree of protection	IP69 IP67 IP66 conforming to IEC 60529 IP69K	
NEMA degree of protection	NEMA 13 NEMA 4X	
IK degree of protection	IK03 conforming to EN 50102	
Standards	EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4 UL 508 EN/IEC 60947-5-5 JIS C 4520 CSA C22.2 No 14	
Product certifications	UL listed CSA	
Vibration resistance	5 gn (12500 Hz) conforming to IEC 60068-2-6	
Shock resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27	

Contractual warranty

Warranty period	18 months

Dimensions



- 2 knock-outs for Pg 13.5 cable gland, maximum capacity 12 mm/0.47 in. Knock-out for cable entry, maximum capacity 14 mm/0.55 in.

Control station fitted with:	c in mm	c in in.
Flush pushbutton	62	2.44
Illuminated pushbutton	64	2.52
Pilot light	65.5	2.58
Projecting pushbutton	66	2.60
Selector switch	80	3.15
Key switch	105.5	4.15