

ZBE1025

single contact block for head Ø22 1NC silver alloy
spring clamp terminals



Main

Range of product	Harmony XB5 Harmony XB4
Product or component type	Contact block
Device short name	ZBE
Sale per indivisible quantity	4
IP degree of protection	IP20 IEC 60529
Contacts type and composition	1 NC
Contacts operation	Slow-break
Contact block type	Single
Contacts usage	Standard contacts
Connections - terminals	Spring clamp terminals

Complementary

Product weight	0.011 kg
Positive opening	With EN/IEC 60947-5-1 appendix K
Operating travel	1.5 mm NC changing electrical state 4.3 mm total travel
Operating force	2 N NC changing electrical state
Mechanical durability	5000000 cycles
Contacts material	Silver alloy (Ag/Ni)
Electrical reliability IEC 60947-5-4	$\Lambda < 10\text{exp}(-8)$ at 17 V, 5 mA in clean environment conforming to EN/IEC 60947-5-4 $\Lambda < 10\text{exp}(-7)$ at 5 V, 1 mA in clean environment conforming to EN/IEC 60947-5-4
Mounting of block	Front mounting
Condition of use	Mounting on push-button collar
Electrical composition code	C11 <= 3 C14 <= 2 M10 <= 2
Compatibility code	ZBE

Environment

Protective treatment	TH
Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...70 °C
Standards	EN/IEC 60947-1 UL 508 EN/IEC 60947-5-4 CSA C22.2 No 14 EN/IEC 60947-5-1 JIS C 4520
Product certifications	RINA DNV UL BV LROS (Lloyds register of shipping) CSA GOST GL CCC
Vibration resistance	5 gn 2...500 Hz IEC 60068-2-6
Shock resistance	30 gn 18 ms half sine wave acceleration IEC 60068-2-27 50 gn 11 ms half sine wave acceleration IEC 60068-2-27

Contractual warranty

Warranty period	18 months
-----------------	-----------