Product datasheet Characteristics

ABT7PDU010G

voltage transformer - 230..400 V - 2 x 115 V - 100 VA



Main

TTG.		;
Range of product	Phaseo Universal	
Product or component type	Safety and isolation transformer	Ť
Rated power in VA	100 VA	5
Input voltage	230 V AC single phase, terminal(s): N-L1 400 V AC phase to phase, terminal(s): L1-L2	ir. Aftho
Output voltage	115/230 V AC	<u> </u>
Secondary winding	Double	
Protective cover	With	
Ambient air temperature for operation	-2060 °C	: <u>:</u>

Complementary

Input voltage limits	360440 V 207253 V	
Network frequency limits	4763 Hz	
Input voltage tolerance	+/- 15 V	
Efficiency	86 %	
Power dissipation in W	16.3 W	
Voltage variation at nominal load	0,0417 at 400 V 4 % at 230 V	
Output sustained overvoltage	0,049 (no load, hot state)	
Voltage drop at rated load	4.23 %	
No load losses	11.26 W	
Short-circuit voltage	0,062	
Output protection type	Against overload, protection technology: external Against overvoltage, protection technology: external Against short-circuits, protection technology: external	-
Connections - terminals	Screw type terminals for input connection, connection capacity: 5 x 4 mm² AWG 11 Screw type terminals for input ground connection, connection capacity: 1 x 4 mm² AWG 11 Screw type terminals for output connection, connection capacity: 4 x 4 mm² AWG 11	F

Marking	CE
Fixing mode	By clips on 35 x 15 mm symmetrical DIN rail By 4 screws, screw(s) \emptyset = 5.5 mm on horizontal panel with derating to 90 % By 4 screws, screw(s) \emptyset = 5.5 mm on vertical panel, operating position: horizontal By 4 screws, screw(s) \emptyset = 5.5 mm on vertical panel, operating position: vertical
Output coupling	Grounding of secondary Series by internal jumper Parallel
Operating altitude	3000 m
Electrical insulation class	Class B
Status LED	Orange for input voltage
Product weight	2.86 kg

Environment

Product certifications	UR EAC
Standards	UL 506
IP degree of protection	IP20
Environmental characteristic	EMC conforming to EN 62041 Safety conforming to EN 61558-1 Safety conforming to EN 61558-2-6
Ambient air temperature for storage	-4080 °C
Relative humidity	095 % during operation
Overvoltage category	Class I conforming to VDE 0106-1
Dielectric strength	3200 V between input and ground 3200 V between output and ground 5100 V between input and output


Contractual warranty

oontractical marranty			
Warranty period	18 months		

Product datasheet Dimensions Drawings

ABT7PDU010G

Dimensions



Dimensions in mm

а	b	С	G	J	Ø	
87	139	108	60	96	5.5	


Dimensions in in.

а	b	С	G	J	Ø
3.42	5.47	4.25	2.36	3.78	0.22

Product datasheet Connections and Schema

ABT7PDU010G


Internal Scheme




Product datasheet Connections and Schema

ABT7PDU010G

Primary Voltage Wiring






Product datasheet Connections and Schema

ABT7PDU010G

Secondary Voltage Wiring



J2, J3ln**tle**rnal Jumper