Product datasheet Characteristics

GC4040M5

TeSys GC - modular contactor - 40 A - 4 NO - coil 220...240 V AC



Main

TeSys	
TeSys GC	- 9
Modular contactor	
GC40	4
Motor control Heating Lighting	
	TeSys GC Modular contactor GC40 Motor control Heating

Complementary

Utilisation category	AC-7A	ininim
	AC-7B	eter
Poles description	4P	for d
Pole contact composition	4 NO	l
[Ue] rated operational voltage	<= 250 V AC	o be
[le] rated operational current	40 A AC-7A 15 A AC-7B	l is not t
Operating position	30°/Vertical	For an
Control circuit type	AC 50 Hz	itute 1
Control circuit voltage	220240 V AC 50 Hz	subst
[Uimp] rated impulse withstand voltage	4 kV	as a
[Ith] conventional free air thermal current	40 A at <= 50 °C for power circuit	 ntended
Irms rated making capacity	120 A at 400 V AC for power circuit conforming to IEC 61095	_ tot
Rated breaking capacity	120 A at 400 V for power circuit conforming to IEC 61095	Lion is
[lcw] rated short-time withstand current	100 A <= 40 °C 30 s power circuit 320 A <= 40 °C 10 s power circuit	cumentar
Associated fuse rating	40 A gL at <= 440 V for power circuit	ls do
Average impedance	2 mOhm at 50 Hz - Ith 40 A for power circuit	e:-
[Ui] rated insulation voltage	500 V conforming to IEC 61095	Sclaim

500 V	conforming	to VDE	0110

Electrical durability	AC-7A : 100000 cycles AC-7B : 100000 cycles	
Control type	Remote control	
Mounting mode	Clip-on	
Mounting support	DIN rail	
Standards	IEC 61095 IEC 60947-5	
Connections - terminals	Control circuit: screw clamp terminals 1 cable(s) 2.5 mm² - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 2 cable(s) 2.5 mm² - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 1 cable(s) 2.5 mm² - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 2 cable(s) 1.5 mm² - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 1 cable(s) 1.5 mm² - cable stiffness: solid - without cable end Control circuit: screw clamp terminals 2 cable(s) 1.5 mm² - cable stiffness: solid - without cable end Power circuit: screw clamp terminals 1 cable(s) 25 mm² - cable stiffness: flexible - without cable end Power circuit: screw clamp terminals 2 cable(s) 16 mm² - cable stiffness: flexible - with cable end Power circuit: screw clamp terminals 2 cable(s) 4 mm² - cable stiffness: flexible - with cable end Power circuit: screw clamp terminals 1 cable(s) 25 mm² - cable stiffness: solid - without cable end Power circuit: screw clamp terminals 2 cable(s) 6 mm² - cable stiffness: solid - without cable end Power circuit: screw clamp terminals 2 cable(s) 6 mm² - cable stiffness: solid - without cable end	
Tightening torque	Control circuit : 0.8 N.m - on screw clamp terminals Power circuit : 2 N.m - on screw clamp terminals	
Operating time	1025 ms opening 1030 ms closing	
Mechanical durability	1000000 cycles	
Operating rate	300 cyc/h at <= 50 °C	
Control circuit voltage limits	0.20.75 Uc at <= 50 °C drop-out 50 Hz 0.851.1 Uc at <= 50 °C operational 50 Hz	
Hold-in power consumption in VA	6.5 VA at 20 °C 50 Hz	
Heat dissipation	2.1 W at 50/60 Hz	

Environment

LITVITOTITICITE	
IP degree of protection	IP20 conforming to VDE 0106 IP40 in enclosure conforming to VDE 0106
Protective treatment	TC
Ambient air temperature for operation	-550 °C
Ambient air temperature for storage	-4070 °C
Operating altitude	<= 3000 m
Mechanical robustness	Vibrations contactor open 2 Gn, 5300 Hz Shocks contactor open 10 Gn for 11 ms Shocks contactor closed 15 Gn for 11 ms Vibrations contactor closed 3 Gn, 5300 Hz
Total number of 18 mm modules	3
Height	85 mm
Width	54 mm
Depth	62.5 mm
Product weight	0.39 kg
Quantity per set	Set of 4
Colour	White

Contractual warranty

Warranty period	18 months