

ZCKE67

limit switch head ZCKE - steel roller plunger reinforced



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product compatibility	XCKJ
Associated body	ZCKJ8H29 ZCKJ21H29 ZCKJ4H7 ZCKJ4 ZCKJ1 ZCKJD35H7 ZCKJ7 ZCKJ7H7 ZCKJD39 ZCKJ2H7 ZCKJD35H29 ZCKJD31H29 ZCKJD39H29 ZCKJD37H7 ZCKJ6 ZCKJ7H29 ZCKJ5H7 ZCKJ1H7 ZCKJ11H7 ZCKJ2 ZCKJD35 ZCKJ5H29 ZCKJ8H7 ZCKJ41 ZCKJ5 ZCKJ1H29 ZCKJ9H7 ZCKJ9H29 ZCKJD39H7 ZCKJ21 ZCKJ11

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCKJ9
 ZCKJD37H29
 ZCKJ21H7
 ZCKJD31
 ZCKJ2H29
 ZCKJD31H7
 ZCKJ8
 ZCKJ6H29
 ZCKJ4H29
 ZCKJ11H29
 ZCKJ41H7
 ZCKJ41H29
 ZCKJ6H7
 ZCKJD37

Movement of operating head	Linear
Type of operator	Roller plunger spring return metal (reinforced)
Type of approach	Lateral approach 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	With
Head material	Metal

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0851 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------