

8406 Multi-Conductor - Three-Conductor, Low-Impedance Cable



For more Information
please call

1-800-Belden1

General Description:

24 AWG stranded (45x40) TC alloy conductors, EPDM rubber insulation, conductive textile wrap (100% coverage), TC braid shield (60% coverage), cotton serve, EPDM rubber jacket.

Physical Characteristics (Overall)**Conductor**

AWG:

# Conductors	AWG	Stranding	Conductor Material	Dia. (in.)
3	24	45x40	Tinned Copper Alloy	.024

Total Number of Conductors:

3

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
EPDM - Ethylene Propylene Diene Monomer Rubber	0.065

Outer Shield

Outer Shield Material:

Layer #	Type	Outer Shield Material	Coverage (%)
1	Tape	Conductive Textile	100
2	Braid	TC - Tinned Copper	60
3	Spiral Serve	Cotton	100

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
EPDM - Ethylene Propylene Diene Monomer Rubber

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	Red
3	White

Overall Nominal Diameter:

0.223 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +90°C

Non-UL Temperature Rating: 90°C

Bulk Cable Weight: 33 lbs/1000 ft.

Max. Recommended Pulling Tension: 67 lbs.

Min. Bend Radius/Minor Axis: 2.250 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2002/95/EC (RoHS): No

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
30

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
55

Nom. Conductor DC Resistance:

8406 Multi-Conductor - Three-Conductor, Low-Impedance Cable

DCR @ 20°C (Ohm/1000 ft)
28.7

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
11.38

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
2.2 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8406 010100	100 FT	4.100 LB	BLACK		3 #24 CS EPDM BRD CS SBR
8406 010500	500 FT	16.500 LB	BLACK		3 #24 CS EPDM BRD,CS SBR

Revision Number: 2 Revision Date: 10-15-2012

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).