


9617 Multi-Conductor - Computer Cable for EIA RS-232 Applications



For more Information
please call

1-800-Belden1



General Description:

24 AWG stranded (7x32) tinned copper conductors, S-R PVC insulation, overall Beldfoil® (100% coverage), TC braid shield (65% coverage), PVC jacket

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
25	24	7x32	TC - Tinned Copper

Total Number of Conductors: 25

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
S-R PVC - Semi-Rigid Polyvinyl Chloride	0.011

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100
2		Braid	TC - Tinned Copper	65

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.037

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	White
3	Red
4	Green
5	Orange
6	Blue
7	White/Black
8	Red/Black
9	Green/Black
10	Orange/Black
11	Blue/Black
12	Black/White
13	Red/White
14	Green/White
15	Blue/White
16	Black/Red
17	White/Red
18	Orange/Red
19	Blue/Red
20	Red/Green
21	Orange/Green
22	Black/White/Red
23	White/Black/Red
24	Red/Black/White
25	Green/Black/White

Overall Nominal Diameter: 0.370 in.

Mechanical Characteristics (Overall)

9617 Multi-Conductor - Computer Cable for EIA RS-232 Applications

Operating Temperature Range:	-30°C to +80°C
UL Temperature Rating:	80°C (UL AWM Style 2464)
Bulk Cable Weight:	89 lbs/1000 ft.
Min. Bend Radius/Minor Axis:	3.750 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG
CEC/(UL) Specification:	CMG
AWM Specification:	UL Style 2464 (300 V 80°C)
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	10/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 FT4 Loading
CSA Flame Test:	FT4

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
30

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
55

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
25

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
5.1

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
1.1 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9617 060100	100 FT	9.700 LB	CHROME		25 #24 PVC SH PVC
9617 0601000	1,000 FT	96.000 LB	CHROME	C	25 #24 PVC SH PVC
9617 060500	500 FT	47.500 LB	CHROME	C	25 #24 PVC SH PVC

Notes:

C = CRATE REEL PUT-UP.

9617 Multi-Conductor - Computer Cable for EIA RS-232 Applications

Revision Number: 3 Revision Date: 09-11-2012

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).