


83506 Multi-Conductor - Audio, Control and Instrumentation Cable



For more Information
please call

1-800-Belden1

**General Description:**

24 AWG stranded (7x32) TC conductors, conductors cabled, plenum, FEP insulated, overall Beldfoil® (100% coverage) + TC braid shield (85% coverage), FEP jacket.

Physical Characteristics (Overall)**Conductor**

AWG:

# Conductors	AWG	Stranding	Conductor Material
6	24	7x32	TC - Tinned Copper

Total Number of Conductors: 6

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
FEP - Fluorinated Ethylene Propylene	.006

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100
2		Braid	TC - Tinned Copper	85

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
FEP - Fluorinated Ethylene Propylene	.014

Overall Cable

Overall Cabling Lay Length & Direction:

Length (in.)
1.75

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	White
3	Red
4	Green
5	Orange
6	Blue

Overall Nominal Diameter: 0.165 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -70°C To +200°C

Bulk Cable Weight: 26 lbs/1000 ft.

Max. Recommended Pulling Tension: 37.200 lbs.

Min. Bend Radius/Minor Axis: 1.750 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification: CMP

CEC/C(UL) Specification: CMP

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

83506 Multi-Conductor - Audio, Control and Instrumentation Cable

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MIL Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: NFPA 262

CSA Flame Test: FT6

Plenum/Non-Plenum

Plenum (Y/N): Yes

Electrical Characteristics (Overall)**Nom. Capacitance Conductor to Conductor:**

Capacitance (pF/ft)

20

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

36

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

24.0

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

5.8

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

1.4 Amps per conductor @ 25°C

Notes (Overall)**Notes:** Plenum Cables, except for Flamarrest® jacket, are suitable for Outdoor and Direct Burial application.**Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
83506 0021000	1,000 FT	28.000 LB	RED	C	6#24 FEP SH FEP
83506 002500	500 FT	15.000 LB	RED	C	6#24 FEP SH FEP

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 08-21-2012

© 2016 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).