

ZCKD21
limit switch head ZCKD - thermoplastic roller lever
plunger horizontal direction



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKD
Head type	Plunger head
Product compatibility	XCKM XCKL
Associated body	ZCKL6 ZCKM1H7 ZCKM8H29 ZCKMD37 ZCKLD35 ZCKL8H7 ZCKL7H7 ZCKM6H29 ZCKMD35 ZCKM7H7 ZCKM9 ZCKM6H7 ZCKMD31H29 ZCKM9H29 ZCKMD37H7 ZCKMD39H7 ZCKMD31H7 ZCKL5H7 ZCKL7 ZCKL1H7 ZCKMD39H29 ZCKL5 ZCKL1 ZCKM1H29 ZCKM6 ZCKLD35H7 ZCKLD39 ZCKM5H7 ZCKM8 ZCKM5

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCKMD35H29
 ZCKMD35H7
 ZCKM5H29
 ZCKLD31H7
 ZCKM8H7
 ZCKM7
 ZCKMD37H29
 ZCKLD31
 ZCKL6H7
 ZCKLD37H7
 ZCKMD39
 ZCKM7H29
 ZCKL8
 ZCKLD37
 ZCKMD31
 ZCKM1
 ZCKLD39H7

Movement of operating head	Linear Rotary
Type of operator	Roller lever plunger spring return thermoplastic
Type of approach	Lateral approach 1 direction


Complementary

Switch actuation	By 30° cam
Positive opening	With
Head material	Plastic

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1012 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------