

## 87777 Multi-Conductor - CMP Rated (Plenum) Cable

For more Information  
please call

1-800-Belden1



### General Description:

22 AWG stranded (7x30) TC conductor, FEP insulation, twisted pairs individually shielded with Beldfoil® (100% coverage), overall jacket per table below, 22 AWG stranded TC drain wire.

### Physical Characteristics (Overall)

#### Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
3	22	7x30	TC - Tinned Copper	.030

Total Number of Conductors: 6

#### Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
FEP - Fluorinated Ethylene Propylene	0.010

Insulation Resistance: 200,000 megaohms/1000 ft. @500 Volts DC (Cond. to Cond.); 75,000 megaohms/1000 ft. @ 500 Volts DC (Cond. to Shield)

#### Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil® (Z-Fold®)	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
22

Inner Shield Drain Wire Stranding: Stranded

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

#### Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

#### Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVDF - Fluorocopolymer	0.014

#### Overall Cable

Overall Nominal Diameter: 0.234 in.

#### Pair

Pair Color Code Chart:

Number	Color
1	Black & Red
2	Black & White
3	Black & Green

### Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +150°C

Bulk Cable Weight: 36 lbs/1000 ft.

Max. Recommended Pulling Tension: 82 lbs.

Min. Bend Radius/Minor Axis: 2.500 in.

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMP

## 87777 Multi-Conductor - CMP Rated (Plenum) Cable

CEC/C(UL) Specification:	CMP
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes

### Flame Test

UL Flame Test:	NFPA 262
CSA Flame Test:	FT6

### Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	8777

### Electrical Characteristics (Overall)

#### Nom. Characteristic Impedance:

Impedance (Ohm)  
50

#### Nom. Inductance:

Inductance (µH/ft)  
0.18

#### Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)  
31

#### Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)  
67

#### Nominal Velocity of Propagation:

VP (%)  
69

#### Nominal Delay:

Delay (ns/ft)  
1.47

#### Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)  
16

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 11.300 Ohm/1000 ft

#### Max. Operating Voltage - UL:

Voltage  
300 V RMS

#### Max. Recommended Current:

Current  
3.5 Amps per conductor @ 25°C

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
87777 0021000	1,000 FT	39.000 LB	RED	C	3 SH PR #22 FEP SOLEF
87777 002500	500 FT	19.500 LB	RED	C	3 SH PR #22 FEP SOLEF

#### Notes:

C = CRATE REEL PUT-UP.

## 87777 Multi-Conductor - CMP Rated (Plenum) Cable

Revision Number: 2    Revision Date: 09-19-2012

© 2016 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).