

9399 Multi-Conductor - Two-Conductor, Low-Impedance Cables



For more Information
please call

1-800-Belden1

General Description:

24 AWG stranded (45x40) BC alloy conductors, EPDM rubber insulation, conductive textile wrap (100% coverage), TC braid shield (65% coverage), cotton spiral, EPDM jacket.

Physical Characteristics (Overall)**Conductor**

AWG:

# Conductors	AWG	Stranding	Conductor Material	Dia. (in.)
2	24	45x40	Bare Copper Alloy	.024

Total Number of Conductors:

2

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
EPDM - Ethylene Propylene Diene Monomer Rubber	0.064

Outer Shield

Outer Shield Material:

Layer #	Type	Outer Shield Material	Coverage (%)
1	Tape	Conductive Textile	100
2	Braid	TC - Tinned Copper	65
3	Spiral Serve	Cotton	

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
EPDM - Ethylene Propylene Diene Monomer Rubber	.020

Overall Cable

Overall Nominal Diameter:

0.200 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +90°C

Non-UL Temperature Rating: 90°C

Bulk Cable Weight: 25 lbs/1000 ft.

Max. Recommended Pulling Tension: 48 lbs.

Min. Bend Radius/Minor Axis: 2 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2002/95/EC (RoHS): No

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
55

Nom. Inductance:

Inductance (µH/ft)
0.019

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
30

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
55

9399 Multi-Conductor - Two-Conductor, Low-Impedance Cables

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
28.7

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
11.38

Max. Operating Voltage - Non-UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
2.2 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9399 001500	500 FT	12.500 LB	BROWN	C	2 #24 EPDM BRD EPDM

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 08-22-2012

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.
Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.
All sales of Belden products are subject to Belden's standard terms and conditions of sale.
Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).