

10GX32 Multi-Conductor - Enhanced Category 6A Bonded-Pair Cable



For more Information
please call

1-800-Belden1



General Description:

CAT6A (625MHz), 4-Bonded-Pair, U/UTP-Unshielded, Riser-CMR, Premise Horizontal Cable, 23 AWG
Solid Bare Copper Conductors, Polyolefin Insulation, Patented Double-H spline, Ripcord, PVC Jacket

Usage (Overall)

Suitable Applications: Premise Horizontal Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422, Noisy Environments, 10G Category 6A, PoE, PoE+

Physical Characteristics (Overall)

Conductor

AWG:

| # Pairs | AWG | Stranding | Conductor Material |
|---------|-----|-----------|--------------------|
| 4 | 23 | Solid | BC - Bare Copper |

Total Number of Conductors: 8

Insulation

Insulation Material:

| Insulation Material |
|---------------------|
| PO - Polyolefin |

Outer Shield

Outer Shield Material:

| Outer Shield Material |
|-----------------------|
| Unshielded |

Outer Jacket

Outer Jacket Material:

| Outer Jacket Material |
|--------------------------|
| PVC - Polyvinyl Chloride |

Overall Cable

Overall Cabling Separator Material: Patented RoundFlex - Double H Cross-Web

Overall Nominal Diameter: 0.295 in.

Pair

Pair Color Code Chart:

| Number | Color |
|--------|------------------------------|
| 1 | White/Blue Stripe & Blue |
| 2 | White/Orange Stripe & Orange |
| 3 | White/Green Stripe & Green |
| 4 | White/Brown Stripe & Brown |

Mechanical Characteristics (Overall)

Storage Temperature Range: -20°C To +75°C

Installation Temperature Range: +5°C To +50°C

Operating Temperature Range: -20°C To +75°C

UL Temperature Rating: 90C

Bulk Cable Weight: 40 lbs/1000 ft.

Max. Recommended Pulling Tension: 45 lbs.

Min. Bend Radius/Minor Axis: 0.600 in.

Min. Bend/Installation: 3 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMR

10GX32 Multi-Conductor - Enhanced Category 6A Bonded-Pair Cable

| | |
|---------------------------------------|---|
| CEC/C(UL) Specification: | CMR |
| EU Directive 2011/65/EU (ROHS II): | Yes |
| EU CE Mark: | Yes |
| EU Directive 2000/53/EC (ELV): | Yes |
| EU Directive 2002/95/EC (RoHS): | Yes |
| EU RoHS Compliance Date (mm/dd/yyyy): | 12/09/2011 |
| EU Directive 2002/96/EC (WEEE): | Yes |
| EU Directive 2003/11/EC (BFR): | Yes |
| CA Prop 65 (CJ for Wire & Cable): | Yes |
| MII Order #39 (China RoHS): | Yes |
| Telecommunications Standards: | Category 6A - TIA 568.C.2 |
| Other Specification: | Third Party Channel Verified to Category 6A |

Applicable Patents:

| |
|------------------|
| Country |
| www.belden.com/p |

Flame Test

| | |
|-------------------|--------------|
| UL Flame Test: | UL1666 Riser |
| C(UL) Flame Test: | FT4 |
| CSA Flame Test: | FT4 |
| IEEE Flame Test: | 1202 |

Suitability

| | |
|------------------------|-------------|
| Suitability - Indoor: | Yes |
| Suitability - Outdoor: | No |
| Suitability - Aerial: | No |
| Suitability - Burial: | No |
| Sunlight Resistance: | No - Indoor |

Plenum/Non-Plenum

| | |
|----------------|--------|
| Plenum (Y/N): | No |
| Plenum Number: | 10GX33 |

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

| |
|----------------------------|
| Capacitance (pF/ft) |
| 17.000 |

Maximum Capacitance Unbalance (pF/100 m): 330

Nominal Velocity of Propagation:

| |
|---------------|
| VP (%) |
| 64.000 |

Maximum Delay:

| |
|-------------------------|
| Delay (ns/100 m) |
| 538 @ 100MHz |

Max. Delay Skew:

| |
|------------------------------|
| Delay Skew (ns/100 m) |
| 30.000 |

Nom. Conductor DC Resistance:

| |
|---------------------------------|
| DCR @ 20°C (Ohm/1000 ft) |
| 7.500 |

Max. Operating Voltage - UL:

| |
|----------------|
| Voltage |
| 300 V RMS |

Maximum DCR Unbalanced:

| |
|---------------------------------|
| DCR Unbalance @ 20°C (%) |
| 2.000 |

10GX32 Multi-Conductor - Enhanced Category 6A Bonded-Pair Cable

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

| Freq. (MHz) | Max. Attenuation (dB/100 m) | Min. NEXT (dB) | Min. PSNEXT (dB) | Min. ACR (dB) | Min. PSACR (dB) | Min RL (dB) |
|-------------|-----------------------------|----------------|------------------|---------------|-----------------|-------------|
| 1 | 2.100 | 75.3 | 73.3 | 73.2 | 71.2 | 20.000 |
| 4 | 3.800 | 66.3 | 64.3 | 62.5 | 60.5 | 23.000 |
| 8 | 5.300 | 61.8 | 59.8 | 56.4 | 54.4 | 24.500 |
| 10 | 5.900 | 60.3 | 58.3 | 54.4 | 52.4 | 25.000 |
| 16 | 7.500 | 57.2 | 55.2 | 49.8 | 47.8 | 25.000 |
| 20 | 8.400 | 55.8 | 53.8 | 47.4 | 45.4 | 25.000 |
| 25 | 9.400 | 54.3 | 52.3 | 45.0 | 43.0 | 25.000 |
| 31.25 | 10.500 | 52.9 | 50.9 | 42.4 | 40.4 | 25.000 |
| 62.5 | 15.000 | 48.4 | 46.4 | 33.4 | 31.4 | 25.000 |
| 100 | 19.100 | 45.3 | 43.3 | 26.2 | 24.2 | 25.000 |
| 200 | 27.600 | 40.8 | 38.8 | 13.2 | 11.2 | 21.000 |
| 250 | 31.100 | 39.3 | 37.3 | 8.3 | 6.3 | 20.500 |
| 300 | 34.300 | 38.1 | 36.1 | 3.9 | 1.9 | 20.100 |
| 350 | 37.200 | 37.1 | 35.1 | N/A | N/A | 19.800 |
| 400 | 40.100 | 36.3 | 34.3 | N/A | N/A | 19.500 |
| 450 | 42.700 | 35.5 | 33.5 | N/A | N/A | 18.900 |
| 500 | 45.300 | 34.8 | 32.8 | N/A | N/A | 18.400 |
| 550 | 47.700 | 34.2 | 32.2 | N/A | N/A | 18.000 |
| 600 | 50.100 | 33.6 | 31.6 | N/A | N/A | 17.600 |
| 625 | 51.200 | 33.4 | 31.4 | N/A | N/A | 17.400 |
| 750 | 56.700 | 32.2 | 30.2 | N/A | N/A | 16.500 |
| 860 | 61.200 | 31.3 | 29.3 | N/A | N/A | 15.800 |

Premise Cable Electrical Table 2:

| Freq. (MHz) | Input (Unfitted) Imp. (Ohms) | Fitted Impedance | Min. ACRF (dB) | Min. PSACRF (dB) |
|-------------|------------------------------|------------------|----------------|------------------|
| 1 | 100 ± 15 | 100 ± 15 | 70.8 | 68.8 |
| 4 | 100 ± 15 | 100 ± 10.4 | 58.8 | 56.8 |
| 8 | 100 ± 15 | 100 ± 8 | 52.7 | 50.7 |
| 10 | 100 ± 15 | 100 ± 7.3 | 50.8 | 48.8 |
| 16 | 100 ± 15 | 100 ± 5 | 46.7 | 44.7 |
| 20 | 100 ± 15 | 100 ± 5 | 44.8 | 42.8 |
| 25 | 100 ± 15 | 100 ± 5 | 42.8 | 40.8 |
| 31.25 | 100 ± 15 | 100 ± 5 | 40.9 | 38.9 |
| 62.5 | 100 ± 15 | 100 ± 5 | 34.9 | 32.9 |
| 100 | 100 ± 15 | 100 ± 5 | 30.8 | 28.8 |
| 200 | 100 ± 22 | 100 ± 5 | 24.8 | 22.8 |
| 250 | 100 ± 32 | 100 ± 5 | 22.8 | 20.8 |
| 300 | 100 ± 32 | 100 ± 5 | 21.3 | 19.3 |
| 350 | 100 ± 32 | 100 ± 5 | 19.9 | 17.9 |
| 400 | 100 ± 32 | 100 ± 5 | 18.8 | 16.8 |
| 450 | 100 ± 32 | 100 ± 5 | 17.7 | 15.7 |
| 500 | 100 ± 32 | 100 ± 5 | 16.8 | 14.8 |
| 550 | 100 ± 32 | 100 ± 5 | 16.0 | 14.0 |
| 600 | 100 ± 32 | 100 ± 5 | 15.2 | 13.2 |
| 625 | 100 ± 32 | 100 ± 5 | 14.9 | 12.9 |
| 750 | | | 13.3 | 11.3 |
| 860 | | | 12.1 | 10.1 |

Premise Cable Electrical Table 4:

| Frequency (MHz) | Min. PSANEXT (dB) | Min. PSAACRF (dB) | Min. TCL (dB) | Min. ELTCTL (dB) |
|-----------------|-------------------|-------------------|---------------|------------------|
| 1.000 | 67.000 | 67.000 | 48.000 | 43.000 |
| 4.000 | 67.000 | 67.000 | 48.000 | 41.000 |
| 8.000 | 67.000 | 61.100 | 48.000 | 24.900 |
| 10.000 | 67.000 | 59.200 | 48.000 | 23.000 |
| 16.000 | 67.000 | 55.100 | 46.000 | 18.900 |
| 20.000 | 67.000 | 53.200 | 45.000 | 17.000 |
| 25.000 | 67.000 | 51.200 | 44.000 | 15.000 |
| 31.250 | 67.000 | 49.300 | 43.100 | |
| 62.500 | 66.600 | 43.300 | 40.000 | |
| 100.000 | 63.500 | 39.200 | 38.000 | |
| 200.000 | 59.000 | 33.200 | 35.000 | |
| 250.000 | 57.500 | 31.200 | 34.000 | |
| 300.000 | 56.300 | 29.700 | 33.200 | |
| 350.000 | 55.300 | 28.300 | 32.600 | |

10GX32 Multi-Conductor - Enhanced Category 6A Bonded-Pair Cable

| | | | | |
|---------|--------|--------|--------|--|
| 400.000 | 54.500 | 27.200 | 32.000 | |
| 450.000 | 53.700 | 26.100 | 31.500 | |
| 500.000 | 53.000 | 25.200 | 31.000 | |
| 550.000 | 52.400 | 24.400 | | |
| 600.000 | 51.800 | 23.600 | | |
| 625.000 | 51.600 | 23.300 | | |
| 750.000 | 50.400 | 21.700 | | |
| 860.000 | 49.500 | 20.500 | | |

Notes (Overall)

Notes: Jacket sequentially marked at 2 ft. intervals. Third party channel verified to TIA/EIA-568-C.2, Category 6A. 0.295" cable dimension per TIA 6@1 equivalent diameter.

Put Ups and Colors:

| Item # | Putup | Ship Weight | Color | Notes | Item Desc |
|----------------|----------|-------------|-------------|-------|---------------------------|
| 10GX32 0041000 | 1,000 FT | 40.000 LB | YELLOW | C | CAT6A 4PRB U/UTP CMR REEL |
| 10GX32 0061000 | 1,000 FT | 40.000 LB | BLUE, LIGHT | C | CAT6A 4PRB U/UTP CMR REEL |
| 10GX32 0081000 | 1,000 FT | 40.000 LB | GRAY | C | CAT6A 4PRB U/UTP CMR REEL |
| 10GX32 0091000 | 1,000 FT | 40.000 LB | WHITE | C | CAT6A 4PRB U/UTP CMR REEL |
| 10GX32 0101000 | 1,000 FT | 40.000 LB | BLACK | | CAT6A 4PRB U/UTP CMR REEL |

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 10 Revision Date: 08-08-2016

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).