



### Main

Range	Multi 9
Product or component type	Undervoltage release
Device short name	MN
Control circuit voltage	24 V AC 50/60 Hz 24 V DC
Control type	Standard
9 mm pitches	2

### Complementary

Local signalling	Action indicator
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Height	82.5 mm
Width	18 mm
Depth	68 mm
Connections - terminals	Pad terminal 1 cable(s) 2.5 mm <sup>2</sup> flexible Pad terminal 1 cable(s) 2.5 mm <sup>2</sup> rigid Pad terminal 2 cable(s) 1.5 mm <sup>2</sup> flexible Pad terminal 2 cable(s) 1.5 mm <sup>2</sup> rigid
Wire stripping length	9 mm
Tightening torque	1 N.m

### Environment

Standards	EN/IEC 60947-5-1
Product certifications	KEMA LCIE ASTA ASEFA
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C

Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0801 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------