

3613 Multi-Conductor - Enhanced Category 6 Nonbonded-Pair Cable



For more Information
please call

1-800-Belden1



General Description:

CAT6+ (400MHz), 4-Pair, U/UTP-Unshielded, Plenum-CMP, Premise Horizontal Cable, 23 AWG Solid Bare Copper Conductors, Dual FRPO/FEP Insulation, Patented X-Spline Center Member, Rip Cord, Flamarrest® PVC jacket.

Usage (Overall)

Suitable Applications: Premise Horizontal Cable, Gigabit Ethernet, POE, POE+, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, Noisy Environments

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	23	Solid	BC - Bare Copper

Total Number of Conductors: 8

Insulation

Insulation Material:

Insulation Material
FRPO/FEP - Flame Retardant Polyolefin/Fluorinated Ethylene Propylene

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material	Nom. Wall Thickness (in.)
Flamarrest(R)	LS PVC - Low Smoke Polyvinyl Chloride	0.017

Outer Jacket Diameter:

Nom. Dia. (in.)
0.235

Outer Jacket Ripcord: Yes

Overall Cable

Overall Cabling Separator Material: Patented X-Spline Center Member

Overall Nominal Diameter: 0.235 in.

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Storage Temperature Range: -20°C To +75°C

Installation Temperature Range: 0°C To +60°C

Operating Temperature Range: 0°C To +75°C

Bulk Cable Weight: 32 lbs/1000 ft.

Max. Recommended Pulling Tension: 45 lbs.

Min. Bend Radius/Minor Axis: 0.750 in.

Min. Bend/Installation: 2.250 in.

3613 Multi-Conductor - Enhanced Category 6 Nonbonded-Pair Cable

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
EU Directive 2011/65/EU (ROHS II):	Yes
Other Standards:	ISO/IEC 11801 ed 2.1 (2008) Class E
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/03/2009
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Telecommunications Standards:	Category 6 - TIA 568.C.2
Other Specification:	6

Applicable Patents:

Country
www.belden.com/p

Flame Test

UL Flame Test:	NFPA 262
C(UL) Flame Test:	FT6

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	No
Suitability - Aerial:	No
Suitability - Burial:	No
Sunlight Resistance:	No

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	3612

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/ft)
15.5

Maximum Capacitance Unbalance (pF/100 m):	330
---	-----

Nominal Velocity of Propagation:

VP (%)
70.000

Maximum Delay:

Freq. (MHz)	Delay (ns/100 m)
100.000	537.600

Typical Delay Skew:

Delay Skew (ns/ft)
35.000

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)
7.700

Max. Operating Voltage - UL:

Voltage
300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)

3613 Multi-Conductor - Enhanced Category 6 Nonbonded-Pair Cable

3.000

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)
0.772	1.800	81.0	81.0	79.2	79.2	
1	2.000	79.3	79.3	77.3	77.3	20.000
4	3.700	70.3	70.3	66.6	66.6	23.000
8	5.200	65.8	65.8	60.6	60.6	24.500
10	5.800	64.3	64.3	58.5	58.5	25.000
16	7.400	61.2	61.2	53.9	53.9	25.000
20	8.300	59.8	59.8	51.5	51.5	25.000
25	9.300	58.3	58.3	49.1	49.1	24.300
31.25	10.400	56.9	56.9	46.5	46.5	23.600
62.5	15.000	52.4	52.4	37.4	37.4	21.500
100	19.300	49.3	49.3	30.0	30.0	20.800
155	24.600	46.4	46.4	21.8	21.8	19.500
200	28.300	44.8	44.8	16.5	16.5	18.700
250	32.100	43.3	43.3	11.2	11.2	18.000
300	35.600	42.1	42.1	6.5	6.5	17.500
350	38.900	41.1	41.1	2.3	2.3	17.000
400	42.000	38.3	38.3	-3.7	-3.7	16.600
450	45.000	37.5	37.5			16.200
500	47.900	36.8	36.8			15.900
550	50.600	36.2	36.2			15.600
600	53.300	35.6	35.6			15.400
650	55.900	35.1	35.1			15.100

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Min. ACRF (dB)	Min. PSACRF (dB)
.772		75.0	73.0
1	100 ± 15	72.8	70.8
4	100 ± 15	60.8	58.8
8	100 ± 15	54.7	52.7
10	100 ± 15	52.8	50.8
16	100 ± 15	48.7	46.7
20	100 ± 15	46.8	44.8
25	100 ± 15	44.8	42.8
31.25	100 ± 15	42.9	40.9
62.5	100 ± 15	36.9	34.9
100	100 ± 15	32.8	30.8
155	100 ± 22	28.9	26.9
200	100 ± 22	26.8	24.8
250	100 ± 32	24.8	22.8
300	100 ± 32	23.3	21.3
350	100 ± 32	21.9	19.9
400	100 ± 32	20.8	18.8
450	100 ± 32	19.7	17.7
500	100 ± 32	18.8	16.8
550	100 ± 32	18.0	16.0
600	100 ± 32	17.2	15.2
650	100 ± 32	16.5	14.5

Premise Cable Electrical Table 4:

Frequency (MHz)	Min. TCL (dB)	Min. ELTCL (dB)
0.772	40.000	37.200
1.000	40.000	35.000
4.000	40.000	23.000
8.000	40.000	16.900
10.000	40.000	15.000
16.000	38.000	10.900
20.000	37.000	9.000
25.000	36.000	7.000
31.250	35.100	
62.500	32.000	
100.000	30.000	
155.000	28.100	
200.000	27.000	

3613 Multi-Conductor - Enhanced Category 6 Nonbonded-Pair Cable

250.000	26.000	
---------	--------	--

Notes (Overall)

Notes: Jacket sequentially marked at 2 ft./1m intervals. Third party verified to ANSI/TIA-568-C.2 Category 6. Values above 400 MHz are for engineering information only.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
3613 D15A1000	1,000 FT	33.000 LB	BLUE		CAT6E 4PR U/UTP CMP RIB
3613 D15U1000	1,000 FT	30.000 LB	BLUE		CAT6E 4PR U/UTP CMP BOX
3613 D151000	1,000 FT	30.000 LB	BLUE		CAT6E 4PR U/UTP CMP REEL
3613 D152500	2,500 FT	70.000 LB	BLUE		CAT6E 4PR U/UTP CMP REEL
3613 002A1000	1,000 FT	33.000 LB	RED		CAT6E 4PR U/UTP CMP RIB
3613 003A1000	1,000 FT	33.000 LB	ORANGE		CAT6E 4PR U/UTP CMP RIB
3613 003U1000	1,000 FT	30.000 LB	ORANGE		CAT6E 4PR U/UTP CMP BOX
3613 0031000	1,000 FT	30.000 LB	ORANGE		CAT6E 4PR U/UTP CMP REEL
3613 004A1000	1,000 FT	33.000 LB	YELLOW		CAT6E 4PR U/UTP CMP RIB
3613 004U1000	1,000 FT	30.000 LB	YELLOW		CAT6E 4PR U/UTP CMP BOX
3613 0041000	1,000 FT	30.000 LB	YELLOW		CAT6E 4PR U/UTP CMP REEL
3613 0042500	2,500 FT	70.000 LB	YELLOW		CAT6E 4PR U/UTP CMP REEL
3613 005A1000	1,000 FT	33.000 LB	GREEN, DARK		CAT6E 4PR U/UTP CMP RIB
3613 005U1000	1,000 FT	30.000 LB	GREEN, DARK		CAT6E 4PR U/UTP CMP BOX
3613 0051000	1,000 FT	30.000 LB	GREEN, DARK		CAT6E 4PR U/UTP CMP REEL
3613 0052500	2,500 FT	70.000 LB	GREEN, DARK		CAT6E 4PR U/UTP CMP REEL
3613 007A1000	1,000 FT	33.000 LB	VIOLET		CAT6E 4PR U/UTP CMP RIB
3613 007U1000	1,000 FT	30.000 LB	VIOLET		CAT6E 4PR U/UTP CMP BOX
3613 008A1000	1,000 FT	33.000 LB	GRAY		CAT6E 4PR U/UTP CMP RIB
3613 008U1000	1,000 FT	30.000 LB	GRAY		CAT6E 4PR U/UTP CMP BOX
3613 0081000	1,000 FT	30.000 LB	GRAY		CAT6E 4PR U/UTP CMP REEL
3613 009A1000	1,000 FT	33.000 LB	WHITE		CAT6E 4PR U/UTP CMP RIB
3613 009U1000	1,000 FT	30.000 LB	WHITE		CAT6E 4PR U/UTP CMP BOX
3613 0091000	1,000 FT	30.000 LB	WHITE		CAT6E 4PR U/UTP CMP REEL
3613 0092500	2,500 FT	70.000 LB	WHITE		CAT6E 4PR U/UTP CMP REEL
3613 010A1000	1,000 FT	33.000 LB	BLACK		CAT6E 4PR U/UTP CMP RIB
3613 010U1000	1,000 FT	30.000 LB	BLACK		CAT6E 4PR U/UTP CMP BOX
3613 0101000	1,000 FT	30.000 LB	BLACK		CAT6E 4PR U/UTP CMP REEL
3613 0102500	2,500 FT	70.000 LB	BLACK		CAT6E 4PR U/UTP CMP REEL
3613 012A1000	1,000 FT	33.000 LB	PINK		CAT6E 4PR U/UTP CMP RIB

Revision Number: 11 Revision Date: 06-09-2016

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).