



HIRSCHMANN


A **BELDEN** BRAND

Product Bulletin

PB 342

Hirschmann® RSP Switches

High-availability network devices that can withstand the toughest conditions and provide the latest authentication and user access security mechanisms.



The RSP Switch Series Supports the New IEC-Standard Redundancy Protocols (PRP, HSR). Networks Can Now be Built With Genuinely Uninterrupted Data Communication.

- Failover time of 0 ms guarantees high productivity for machines and systems
- Extensive security functions guarantee all-round protection against unauthorized intrusions and operator errors
- Precise synchronization enables applications to comply with stringent real-time requirements

The new RSP switches provide robust hardware and a powerful operating system and can withstand extremely harsh environmental conditions. The integration of new redundancy protocols allows uninterrupted data communication.

These new techniques, PRP (Parallel Redundancy Protocol) and HSR (High-availability Seamless Redundancy), are based on the international IEC62439 standard to guarantee future security and interoperability. Precision timing with IEEE 1588v2, synchronizes sensors, drives and measuring equipment. Gigabit Ethernet provides a fast connection to the backbone, while connections to terminal equipment use 100 BASE-TX or 100 BASE-FX.

Applications

The RSP switches are optimized for environments such as the power utility industry where downtime is not an option. The RSP switches guarantee uninterrupted communication under the harshest conditions.


The RSP switches offer optimum solutions wherever uninterrupted data communication is of the essence, as in mechanical engineering, production or security applications.

Benefits

The RSP switches are the first to allow uninterrupted data communication to ensure continuous access to machines and systems in order to increase productivity and profitability. The switches feature comprehensive security functions to provide all-round protection against unauthorized access. Since they also support precise synchronization, they can be used to safely network applications that are subject to stringent real-time requirements.



RSP Switches at a Glance





RSP switches offer eleven ports, three of which can be equipped with SFP transceivers that support Fast (100 BASE-FX) or – optionally – Gigabit-Ethernet (100/1000 BASE-FX). The remaining ports can be used either for 100 BASE-TX or as a combination of four SFP transceivers and four TX ports. These switches have extensive management and redundancy methods, as well as enhanced security mechanisms. In addition, a version is available to precise synchronization compliant with IEEE 1588v2, plus PRP (Parallel Redundancy Protocol) and HSR (High-availability Seamless Redundancy).

Advantages at a Glance:

- Extensive range of redundancy methods: PRP, HSR, PRP/HSR Red Box, MRP, Fast MRP, RSTP
- Precise synchronization compliant with IEEE 1588v2
- Enhanced security mechanisms: authentication, radius, role based access, port security, SSHv2, HTTPS and SFTP, plus others currently in preparation.
- Fast device replacement, comprehensive logging and storage of all configuration data, plus operating software updates via SD card
- High level of vibration resistance
- Broad immunity to electrostatic discharges and magnetic fields
- Temperature range from -40°C to +70°C
- Power supply 24/36/48 V DC or 60/120/250 V DC and 110/230 V AC
- Strong and compact metal housing

0 ms switchover time – the RSP switches support the redundancy protocols PRP and HSR.





RSP Switches Technical Specifications

Product Description				
Type	RSP20-xx	RSP30-xx	RSP25-xx	RSP35-xx
Description	Managed, Industrial Switch DIN Rail, fanless design			
Port Type and Quantity	Ports in total: 11, 3 x FE SFP slots, 4 x FE SFP/4 x10/100 TX ports, or 8 x10/100 TX ports	Ports in total: 11, 3 x FE/GE SFP slots, 4 x FE SFP/4 x10/100 TX ports, or 8 x10/100 TX ports	Ports in total: 11, 3 x FE SFP slots, 4 x FE SFP/4 x10/100 TX ports, or 8 x10/100 TX ports	Ports in total: 11, 3 x FE/GE SFP slots, 4 x FE SFP/4 x10/100 TX ports, or 8 x10/100 TX ports
Additional Interfaces				
V.24 Interface	1x RJ11 socket			
SD Card Slot	1x to connect auto-configuration adapter ACA31 (SD-card)			
Gigabit Ethernet Network Size				
Multimode Fiber (MM)	50/125 μm , 0 – 550 m, 7.5 dB link budget; 62.5/125 μm 0 – 275 m, 7.5 dB link budget (with M-SFP-SX/LC)			
Single Mode Fiber (SM) 9/125 μm	0 – 20 km, 11 dB link budget (with M-SFP-LX/LC); 14 – 42 km, 5 – 20 dB link budget (with M-SFP-LX+/LC)			
Single Mode Fiber (LH) 9/125 μm	24 – 72 km, 6 – 22 dB link budget (with M-SFP-LH/LC); 70 – 128 km, 15 – 30 dB link budget (with M-SFP-LH+/LC)			
Fast Ethernet Network Size				
Twisted Pair	0 – 100 m			
Multimode Fiber (MM)	50/125 μm , 0 – 5000 m, 8 dB link budget; 62.5/125 μm , 0 – 4000 m, 11 dB link budget (with M-Fast SFP-MM/LC)			
Single Mode Fiber (SM) 9/125 μm	0 – 25 km, 13 dB link budget (with M-Fast SFP-SM/LC); 25 – 65 km, 10 – 29 dB link budget (with M-Fast SFP-SM+/LC)			
Single Mode Fiber (LH) 9/125 μm	40 – 104 km, 10 – 29 dB link budget (with M-Fast SFP-LH/LC)			
Network Size – Cascadability				
Line-/Star Topology	any			
Ring Structure	>200 Switches			
Fault Recovery Time	0 ms with PRP or HSR			
Power Requirements				
Operating Voltage	24/36/48 V DC redundant, or 60/120/250 V DC and 110/230 V AC			
Software				
Management	V.24, Telnet, SSHv2, HTTP, HTTPS, TFTP, SFTP, SNMP v1/v2/v3, Traps			
Diagnostics	LED, persistent logging, syslog, signal contact, device status indication, port mirroring N:1, RMON (1,2,3,9), TCPDump, LLDP, copper cable test, SFP management (temperature, optical input and output power), switch dump, configuration check dialog, system information, self tests on cold start, system monitor 1			
Configuration	Command line interface (CLI), web based management, full featured MIB support, BOOTP/DHCP client with auto configuration, HiDiscovery, auto-configuration adapter ACA31 (SD card), Automatic configuration undo (roll-back), text based configuration file, CLI scripting			
Security	MAC based port security, Authentication (IEEE802.1x), Guest/unauthenticated VLAN, Radius client, Restricted management access, Local user accounts, different privilege levels, management authentication via RADIUS, account locking, configurable password policy, account locking, audit trail, configurable login attempts, HTTPS certificate management, CLI/SNMP logging			
Redundancy Functions	MRP, RSTP 802.1w, further protocols in preparation			
Enhanced Redundancy Functions	–	–	Fast MRP, PRP, HSR (pending)	Fast MRP, PRP, HSR (pending)
Filter	QoS (8 classes), CoS queue management, interface trust mode, TOS/DSCP prioritization, port priority (IEEE802.1D/p), VLAN (IEEE802.1Q), IGMP snooping/querier per VLAN (v1/v2/v3), unknown multicast filtering, independent VLAN learning, static unicast/multicast address entries, fast aging			
Time Synchronization	PTPv2 TC two-step, SNTP server and client, Buffered RTC			
Flow Control	Flow control (IEEE802.3X), egress interface shaping, ingress storm protection			
Miscellaneous	Port power down, cable crossing, dual image support, VLAN unaware mode, access to management restricted by VLAN			
Ambient Conditions				
Operating Temperature	0°C to 60°C or -40°C to +70°C, IEC 60068-2-2 Dry Heat Test +85°C, 16 Hours, optional conformal coating			
Relative Humidity (non-condensing)	10% to 95%			
Mechanical Construction				
Dimensions (WxHxD)	90 (98) x 164 x 120 mm (EEC)			
Weight	1.2 kg, (1.5 kg EEC)			
Protection Class	IP30			
Approvals				
Safety of Industrial Control Equipment	cUL 508 (pending)			
Substation	IEEE61850-3, IEEE1613			
Transportation	NEMA TS2 (pending), EN50121-4 (pending)			



RSP Series Managed Industrial DIN Rail Switch Configurator

Fast and Gigabit Ethernet Networks

RSP 3 5 - 08 03 306 TT - E K9 Y9 HP E 2R XX.X XX

Design/Models

RSP- = Rail Switch Power

Data Rates

2 = 10/100 Mbit Ports

3 = 10/100 Mbit and 10/100/1000 Mbit Ports

Hardware Type

0 = Standard

5 = Enhanced Redundancy (PRP, Fast MRP, HSR*), Hardware IEEE1588 v2

Number of 10/100 Mbit Ethernet Ports

08 = 8 x 10/100 Mbit/s

11 = 11x 10/100 Mbit/s

Number of 10/100/1000 Mbit Ethernet Ports

00 = None

03 = 3x 10/100/1000 Mbit/s

Uplink Ports

3Z6 = 1 x 3x SFP slot (100 Mbit)

306 = 3x SFP slot (1000 Mbit)

Port Configuration

TT = All Twisted Pair / RJ45

ZT = 4x SFP slot (100 Mbit) ; 4x (100Mbit) Twisted Pair / RJ45

Temperature Range

S = Standard 0°C to 60°C

T = Extended -40°C to 70°C

E = Extended -40°C to 70°C & Conformal Coating

Voltage Range

CC = 2 x 24/36/48 VDC (18 -60VDC)

K9 = 1x 60/110/125/220/250 VDC (48V - 320 VDC) and 110/120/220/230 VAC (88 - 265 VAC)

Approvals

Z9 = CE; FCC; EN61131

Y9 = "Z9" + cUL508

V9 = "Z9" + IEC 61850; IEEE1613

VY = "V9" + cUL508

Factory Default Redundancy Configuration

HS = Standard

HM = Fast MRP

HP = PRP

Software Configuration

H = Standard

E = Enhanced Encryption

Software Level

2R = Layer 2 Rail Switch Power Software

Software Version

01.0 = Software version 01.0

XX.X = Newest Software Version

Bugfix

0 = Bugfix version 00

XX = Newest Bugfix Version