



Main

Range	TeSys
Device short name	GVAD
Product or component type	Auxiliary contact block
Product compatibility	GV2LE GV2P GV2L GV2RT GV2ME GV3P GV3L
Auxiliary contacts operation	Fault signal 1 NO
Pole contact composition	2 NO
Connections - terminals	Screw clamp terminals 1 cable 0.75...2.5 mm ² - cable stiffness: flexible - without cable end Screw clamp terminals 2 cable 0.75...2.5 mm ² - cable stiffness: flexible - without cable end Screw clamp terminals 2 cable 0.75...1.5 mm ² - cable stiffness: flexible - with cable end Screw clamp terminals 1 cable 0.75...1.5 mm ² - cable stiffness: flexible - with cable end Screw clamp terminals 1 cable 1...2.5 mm ² - cable stiffness: solid Screw clamp terminals 2 cable 1...2.5 mm ² - cable stiffness: solid

Complementary

Mounting location	Left side
[Ui] rated insulation voltage	690 V - conforming to IEC 60947-1 300 V - conforming to UL 508 300 V - conforming to CSA C22.2 No 14
[Ue] rated operational voltage	48...690 V AC 24...240 V DC
[Ith] conventional free air thermal current	2.5 A for fault signalling 6 A
Protection type	GB2CB... circuit breaker rating according to operational current for Ue ≤ 415 V GG fuse ≤ 10 A
Mechanical durability	100000 cycles
Minimum switching current	5 mA

Minimum switching voltage	17 V
Rated operational power in VA	300 VA at 48 V AC-15 - electrical durability: 100000 cycles 400 VA at 690 V AC-15 - electrical durability: 100000 cycles 500 VA at 110...127 V AC-15 - electrical durability: 100000 cycles 500 VA at 500 V AC-15 - electrical durability: 100000 cycles 650 VA at 440 V AC-15 - electrical durability: 100000 cycles 720 VA at 230...240 V AC-15 - electrical durability: 100000 cycles 850 VA at 380...415 V AC-15 - electrical durability: 100000 cycles 36 VA at 24 V AC-14 - electrical durability: 1000 cycles 48 VA at 48 V AC-14 - electrical durability: 1000 cycles 72 VA at 110...127 V AC-14 - electrical durability: 1000 cycles
Rated operational power in W	120 W at 240 V DC-13 - electrical durability: 100000 cycles 140 W at 110 V DC-13 - electrical durability: 100000 cycles 140 W at 24 V DC-13 - electrical durability: 100000 cycles 180 W at 60 V DC-13 - electrical durability: 100000 cycles 240 W at 48 V DC-13 - electrical durability: 100000 cycles 15 W at 48 V DC-13 - electrical durability: 1000 cycles 24 W at 24 V DC-13 - electrical durability: 1000 cycles 9 W at 60 V DC-13 - electrical durability: 1000 cycles
Tightening torque	<= 1.4 N.m - on screw clamp terminals
Height	89 mm
Width	9.3 mm
Depth	66 mm
Product weight	0.055 kg

Environment

Environmental characteristic	Normal environment
------------------------------	--------------------

Contractual warranty

Warranty period	18 months
-----------------	-----------