

For more Information
please call

1-800-Belden1



General Description:

Surveillance & CCTV Cable, mini-RG59, Rated-CM, 25 AWG solid bare copper, foamed polyolefin core, 94% bare copper braid, PVC jacket

Usage (Overall)

Suitable Applications: Analog/Video CCTV

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	25	Solid	BC - Bare Copper	.018

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
Gas-injected FPE - Foam Polyethylene	.085

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	BC - Bare Copper	94

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.146 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +75°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 16 lbs/1000 ft.

Max. Recommended Pulling Tension: 28 lbs.

Min. Bend Radius/Minor Axis: 1.500 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CM

NEC Articles: 800

CEC/C(UL) Specification: CM

EU Directive 2011/65/EU (RoHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

573945 Coax - Surveillance and CCTV Applications

RG Type: Mini 59/U

Series Type: Series 59

Flame Test

UL Flame Test: UL1685 UL Loading

C(UL) Flame Test: FT1

Suitability

Suitability - Indoor: Yes - All colors

Suitability - Outdoor: Yes - Black only

Suitability - Burial: No

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

75

Nom. Inductance:

Inductance (µH/ft)

.109

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)

16.9

Nominal Velocity of Propagation:

VP (%)

80

Nominal Delay:

Delay (ns/ft)

1.27

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

31.0

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

5.6

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1	.45
5	.90
10	1.3
50	3.0
100	4.1
200	6.0
400	8.6
700	11.6
900	13.5
1000	14.5

Max. Operating Voltage - UL:

Voltage

300 V RMS

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
573945 001U1000	1,000 FT	16.000 LB	BROWN		#25 GIFHDPE BRD PVC
573945 0021000	1,000 FT	16.000 LB	RED	C	#25 GIFHDPE BRD PVC
573945 0041000	1,000 FT	16.000 LB	YELLOW		#25 GIFHDPE BRD PVC
573945 0051000	1,000 FT	16.000 LB	GREEN, DARK	C	#25 GIFHDPE BRD PVC
573945 006U1000	1,000 FT	16.000 LB	BLUE, LIGHT		#25 GIFHDPE BRD PVC
573945 0061000	1,000 FT	16.000 LB	BLUE, LIGHT	C	#25 GIFHDPE BRD PVC
573945 0091000	1,000 FT	16.000 LB	WHITE	C	#25 GIFHDPE BRD PVC
573945 010U1000	1,000 FT	16.000 LB	BLACK		#25 GIFHDPE BRD PVC
573945 0101000	1,000 FT	16.000 LB	BLACK	C	#25 GIFHDPE BRD PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 03-11-2013

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).