Product datasheet Characteristics

RM17TG00

phase control relay RM17-T - range 183..528 V AC



Main

IVIAIII			
Range of product	Zelio Control		
Product or component type	Modular measurement and control relays		
Relay type	Control relay		
Product specific application	For 3-phase supply		
Relay name	RM17TG		
Relay monitored parameters	Phase sequence Phase failure detection		
Switching capacity in VA	1250 VA		

Complementary

12 17 10				
<i>M</i> ain				
Range of product	Zelio Control			
Product or component type	Modular measurement and control relays			
Relay type	Control relay			
Product specific application	For 3-phase supply			
Relay name	RM17TG			
Relay monitored parameters	Phase sequence Phase failure detection			
Switching capacity in VA	1250 VA			
Complementary				
Maximum switching voltage	250 V AC 250 V DC			
Minimum switching current	10 mA at 5 V DC			
Supply voltage limits	183528 V AC			
Control circuit voltage limits	- 12 % + 10 % Un			
Power consumption in VA	<= 22 VA at 400 V AC 50 Hz			
Voltage detection threshold	< 100 V for phase failure AC			
Control circuit frequency	5060 Hz +/- 10 %			
Output contacts	1 C/O			
Nominal output current	5 A			
Run-up delay at power-up	<= 650 ms			
Voltage range	183528 V			
Response time	<= 130 ms in the event of a fault			
Marking	CE			
Overvoltage category	III conforming to IEC 60664-1			
nsulation resistance	> 500 MOhm at 500 V DC conforming to IEC 60255-5 > 500 MOhm at 500 V DC conforming to IEC 60664-1			
[Ui] rated insulation voltage	400 V conforming to IEC 60664-1			

50/60 Hz +/- 10 %		
Any position without		
Screw terminals 1 x 0.51 x 4 mm² - AWG 20AWG 11, solid cable without cable end Screw terminals 2 x 0.52 x 2.5 mm² - AWG 20AWG 14, solid cable without cable end Screw terminals 1 x 0.21 x 2.5 mm² - AWG 24AWG 12, flexible cable with cable end Screw terminals 2 x 0.22 x 1.5 mm² - AWG 24AWG 16, flexible cable with cable end		
0.61 N.m conforming to IEC 60947-1		
Self-extinguishing plastic		
LED yellow for relay ON		
35 mm symmetrical DIN rail conforming to EN/IEC 60715		
100000 cycles		
<= 30000000 cycles		
<= 360 operations/hour under full load		
AC-12 conforming to IEC 60947-5-1 AC-13 conforming to IEC 60947-5-1 AC-14 conforming to IEC 60947-5-1 AC-15 conforming to IEC 60947-5-1 DC-12 conforming to IEC 60947-5-1 DC-13 conforming to IEC 60947-5-1		
MTTFd = 924.6 years B10d = 850000		
17.5 mm		
0.13 kg		

Environment

Electromagnetic compatibility	Emission standard for industrial environments conforming to EN/IEC 61000-6-4 Emission standard for residential, commercial and light-industrial environments conforming to EN/IEC 61000-6-3	
	Immunity for industrial environments conforming to EN/IEC 61000-6-2	
Standards	EN/IEC 60255-1	
Product certifications	CSA	
	GL	
	C-Tick	
	GOST	
	UL	
Directives	89/336/EEC - electromagnetic compatibility	
	73/23/EEC - low voltage directive	
Ambient air temperature for storage	-4070 °C	
Ambient air temperature for operation	-2050 °C	
Relative humidity	95 % at 55 °C conforming to IEC 60068-2-30	
Vibration resistance	0.35 mm (f = 557.6 Hz) conforming to IEC 60068-2-6	
	1 gn (f = 57.6150 Hz) conforming to IEC 60255-21-1	
Shock resistance	15 gn for 11 ms conforming to IEC 60255-21-1	
IP degree of protection	IP20 (terminals) conforming to IEC 60529 IP30 (casing) conforming to IEC 60529	
Pollution degree	3 conforming to IEC 60664-1	
Dielectric test voltage	2 kV 1 min AC 50 Hz	
Non-dissipating shock wave	4 kV	

Offer Sustainability

Sustainable offer status	Green Premium product	
RoHS (date code: YYWW)	Compliant - since 0701 - Schneider Electric declaration of conformity	
	Schneider Electric declaration of conformity	
REACh	Reference not containing SVHC above the threshold	
	Reference not containing SVHC above the threshold	
Product environmental profile	Available	
	🚰 End of life manual	


Product end of life instructions	Available	
Contractual warranty		
Warranty period	18 months	

Product datasheet Dimensions Drawings

RM17TG00

3-Phase Supply Control Relays

Dimensions and Mounting




Product datasheet Connections and Schema

RM17TG00

3-Phase Supply Control Relays

Wiring Diagram




Product datasheet Connections and Schema

RM17TG00

Application Scheme

Example




(1) Fault

RM17TG00

Function Diagram

Phase Sequence Control and Total Loss of Phase Detection



Legend

Tr Response time on appearance of a fault

L1, L2, L3 Phases of the supply voltage monitored

R - R1/R2 Output relay(s),

Relay status: black color = energized.