

7893A Multi-Conductor - Multi-Pair Cable

For more Information
please call

1-800-Belden1

**General Description:**

26 AWG stranded tinned copper conductor, Datalene® insulation, pairs individually shielded with bonded Beldfoil® with a drain wire and have numbered and color-coded PVC jackets, overall Beldfoil® shield/drain wire + overall PVC jacket with nylon rip cord

Physical Characteristics (Overall)**Conductor**

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
16	26	7x34	TC - Tinned Copper	.019

Total Number of Conductors: 32

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Dia. (in.)
Datalene®	FHDPE - Foam High Density Polyethylene	.054

Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil®	Tape	Bonded Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
26

Inner Shield Drain Wire Stranding: Stranded

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Dia. (in.)
PVC - Polyvinyl Chloride	.136

Inner Jacket Color Code Chart:

Number	Color
1	Brown and Numbered 1
2	Red and Numbered 2
3	Orange and Numbered 3
4	Yellow and Numbered 4
5	Green and Numbered 5
6	Blue and Numbered 6
7	Purple and Numbered 7
8	Gray and Numbered 8
9	White and Numbered 9
10	Black and Numbered 10
11	Tan and Numbered 11
12	Pink and Numbered 12
13	Gray/Brown Stripe and Numbered 13
14	Gray/Red Stripe and Numbered 14
15	Gray/Orange Stripe and Numbered 15
16	Gray/Yellow Stripe and Numbered 16

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
-----	-----------	-------------------------------

7893A Multi-Conductor - Multi-Pair Cable

26	Stranded	TC - Tinned Copper
----	----------	--------------------

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Ripcord: Yes

Overall Cable

Overall Nominal Diameter: 0.770 in.

Pair

Pair Color Code Chart:

Number	Color
1	Red & Black
2	Red & Black
3	Red & Black
4	Red & Black
5	Red & Black
6	Red & Black
7	Red & Black
8	Red & Black
9	Red & Black
10	Red & Black
11	Red & Black
12	Red & Black
13	Red & Black
14	Red & Black
15	Red & Black
16	Red & Black

Pair Lay Length & Direction:

Lay Length (in.)
1.0

Mechanical Characteristics (Overall)

Operating Temperature Range:	-30°C To +80°C
Bulk Cable Weight:	198 lbs/1000 ft.
Max. Recommended Pulling Tension:	171 lbs.
Min. Bend Radius/Minor Axis:	7.750 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 UL Loading
C(UL) Flame Test:	FT4

Plenum/Non-Plenum

Plenum (Y/N): No

Surface Printing (Overall)

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
110

Nom. Inductance:

Inductance (μH/ft)
.25

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
12.5

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
25.0

Nominal Velocity of Propagation:

VP (%)
76

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
37.3

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C:	25.500 Ohm/1000 ft
---	--------------------

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
.384	.84
.7056	1.14
.768	1.18
1.024	1.34
1.4112	1.50
1.536	1.54
2.048	1.69
2.8224	1.86
3.0720	1.92
4.096	2.14
5.6448	2.40
6.144	2.47
8.192	2.75
11.2896	3.09
12.288	3.18
24.576	4.20

Notes (Overall)

Notes: Pair jackets and shields are bonded so both strip simultaneously with automatic stripping equipment. Datalene® insulation features include low dielectric constant and a dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7893A Z4B1000	1,000 FT	240.000 LB	VIO Z4B	C	16 #26 FHDPE FSPR PVC FS PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 04-15-2008

© 2016 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).