




Typical Applications

The HMC311ST89(E) is ideal for:

- Cellular / PCS / 3G
- Fixed Wireless & WLAN
- CATV & Cable Modem
- Microwave Radio

Functional Diagram



HMC311ST89 / 311ST89E

InGaP HBT GAIN BLOCK MMIC AMPLIFIER, DC - 6 GHz

Features

P1dB Output Power: +15.5 dBm Output IP3: +31.5 dBm Gain: 16 dB 50 Ohm I/O's Industry Standard SOT89 Package Included in the HMC-DK001 Designer's Kit

General Description

The HMC311ST89(E) is a GaAs InGaP Heterojunction Bipolar Transistor (HBT) Gain Block MMIC SMT DC to 6 GHz amplifier. Packaged in an industry standard SOT89, the amplifier can be used as either a cascadable 50 Ohm gain stage or to drive the LO of HMC mixers with up to +16.5 dBm output power. The HMC311ST89(E) offers 16 dB of gain and an output IP3 of +31.5 dBm while requiring only 54 mA from a +5V supply. The Darlington feedback pair used results in reduced sensitivity to normal process variations and yields excellent gain stability over temperature while requiring a minimal number of external bias components.

Electrical Specifications, Vs= 5V, Rbias= 22 Ohm, $T_A = +25^{\circ}$ C

| Parameter | | Min. | Тур. | Max. | Units |
|--|---|----------------------|-------------------------|-------------------------|----------------------------|
| Gain | DC - 1.0 GHz 1.0 - 4.0 GHz 4.0 - 6.0 GHz | 14.0 13.0 12.5 | 16.0 15.0 14.5 | | dB dB dB |
| Gain Variation Over Temperature | DC - 2.0 GHz 2.0 - 4.0 GHz 4.0 - 6.0 GHz | | 0.004 0.007 0.012 | 0.007 0.012 0.016 | dB/ °C dB/ °C dB/ °C |
| Return Loss Input / Output | DC - 2.0 GHz 2.0 - 5.0 GHz 5.0 - 6.0 GHz | | 8 7 8 | | dB dB dB |
| Reverse Isolation | DC - 6 GHz | | 20 | | dB |
| Output Power for 1 dB Compression (P1dB) | DC - 2.0 GHz 2.0 - 4.0 GHz 4.0 - 6.0 GHz | 13.5 12.0 10.0 | 15.5 15.0 13.0 | | dBm dBm dBm |
| Output Third Order Intercept (IP3) | DC - 1.0 GHz 1.0 - 2.0 GHz 2.0 - 4.0 GHz 4.0 - 6.0 GHz | | 31.5 30 27 24 | | dBm dBm dBm dBm |
| Noise Figure | DC - 4 GHz 4.0 - 6.0 GHz | | 4.5 5 | | dB |
| Supply Current (Icq) | | | 55 | 74 | mA |

Note: Data taken with broadband bias tee on device output.

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.

HMC311ST89* PRODUCT PAGE QUICK LINKS

Last Content Update: 02/23/2017

COMPARABLE PARTS

View a parametric search of comparable parts.

EVALUATION KITS

HMC311ST89 Evaluation Board

DOCUMENTATION

Application Notes

- AN-1363: Meeting Biasing Requirements of Externally Biased RF/Microwave Amplifiers with Active Bias Controllers
- Broadband Biasing of Amplifiers General Application Note
- MMIC Amplifier Biasing Procedure Application Note
- Thermal Management for Surface Mount Components General Application Note

Data Sheet

HMC311ST89 Data Sheet

TOOLS AND SIMULATIONS \square

• HMC311ST89 S-Parameters

REFERENCE MATERIALS

Quality Documentation

- Package/Assembly Qualification Test Report: 3 Lead Plastic SOT89 Package (QTR: 10002 REV: 02)
- PCN: MS, QS, SOT, SOIC packages Sn/Pb plating vendor change
- Semiconductor Qualification Test Report: GaAs HBT-B (QTR: 2013-00229)

DESIGN RESOURCES

- HMC311ST89 Material Declaration
- PCN-PDN Information
- Quality And Reliability
- Symbols and Footprints

DISCUSSIONS

View all HMC311ST89 EngineerZone Discussions.

SAMPLE AND BUY

Visit the product page to see pricing options.

TECHNICAL SUPPORT

Submit a technical question or find your regional support number.


DOCUMENT FEEDBACK

Submit feedback for this data sheet.







Broadband Gain & Return Loss



Input Return Loss vs. Temperature




Reverse Isolation vs. Temperature






InGaP HBT GAIN BLOCK MMIC AMPLIFIER, DC - 6 GHz


Gain vs. Temperature



Output Return Loss vs. Temperature



Noise Figure vs. Temperature




8

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.







P1dB vs. Temperature



Power Compression @ 1 GHz




Output IP3 vs. Temperature




HMC311ST89 / 311ST89E

InGaP HBT GAIN BLOCK MMIC AMPLIFIER, DC - 6 GHz


Psat vs. Temperature



Power Compression @ 6 GHz



Gain, Power, OIP3 & Supply Current vs. Supply Voltage @ 1 GHz



Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.





Absolute Maximum Ratings

| Collector Bias Voltage (Vcc) | +7V | |
|---|----------------|--|
| RF Input Power (RFIN)(Vcc = +3.9V) | +10 dBm | |
| Junction Temperature | 150 °C | |
| Continuous Pdiss (T = 85 °C) (derate 5.21 mW/°C above 85 °C) | 0.34 W | |
| Thermal Resistance (junction to lead) | 191 °C/W | |
| Storage Temperature | -65 to +150 °C | |
| Operating Temperature | -40 to +85 °C | |




HMC311ST89 / 311ST89E


MMIC AMPLIFIER, DC - 6 GHz

InGaP HBT GAIN BLOCK

Outline Drawing







NOTES:

1. PACKAGE BODY MATERIAL:

MOLDING COMPOUND MP-180S OR EQUIVALENT.

2. LEAD MATERIAL: Cu w/ Ag SPOT PLATING.

3. LEAD PLATING: 100% MATTE TIN.

4. DIMENSIONS ARE IN INCHES [MILLIMETERS]

DIMENSION DOES NOT INCLUDE MOLDFLASH OF 0.15mm PER SIDE. DIMENSION DOES NOT INCLUDE MOLDFLASH OF 0.25mm PER SIDE. 7. ALL GROUND LEADS MUST BE SOLDERED TO PCB RF GROUND.

Package Information

| Part Number | Package Body Material | Lead Finish | MSL Rating | Package Marking ^[3] |
|-------------|--|---------------|---------------------|--------------------------------|
| HMC311ST89 | Low Stress Injection Molded Plastic | Sn/Pb Solder | MSL1 ^[1] | H311 XXXX |
| HMC311ST89E | RoHS-compliant Low Stress Injection Molded Plastic | 100% matte Sn | MSL1 ^[2] | <u>H311</u> XXXX |

[1] Max peak reflow temperature of 235 °C

[2] Max peak reflow temperature of 260 $^\circ\text{C}$

[3] 4-Digit lot number XXXX

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.



HMC311ST89 / 311ST89E


InGaP HBT GAIN BLOCK MMIC AMPLIFIER, DC - 6 GHz



Pin Descriptions

| Pin Number | Function | Description | Interface Schematic |
|------------|----------|---|---------------------|
| 1 | RFIN | This pin is DC coupled. An off chip DC blocking capacitor is required. | RFOUT |
| 3 | RFOUT | RF output and DC Bias for the output stage. | |
| 2, 4 | GND | These pins and package bottom must be connected to RF/ DC ground. | |

Application Circuit



Recommended Component Values

| Component | | | | | ncy (MHz) | | | |
|-----------|---------|--------|--------|--------|-----------|--------|--------|--------|
| Component | 50 | 900 | 1900 | 2200 | 2400 | 3500 | 5200 | 5800 |
| L1 | 270 nH | 56 nH | 18 nH | 18 nH | 15 nH | 8.2 nH | 3.3 nH | 3.3 nH |
| C1, C2 | 0.01 µF | 100 pF | 100 pF | 100 pF | 100 pF | 100 pF | 100 pF | 100 pF |

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.




HMC311ST89 / 311ST89E

InGaP HBT GAIN BLOCK MMIC AMPLIFIER, DC - 6 GHz



Evaluation PCB



v03.0710

List of Materials for Evaluation PCB 108313 [1]

| Item | Description |
|---------|------------------------------|
| J1 - J2 | PCB Mount SMA Connector |
| J3 - J4 | DC Pin |
| C1, C2 | Capacitor, 0402 Pkg. |
| C3 | 100 pF Capacitor, 0402 Pkg. |
| C4 | 1000 pF Capacitor, 0603 Pkg. |
| C5 | 2.2 µF Capacitor, Tantalum |
| R1 | Resistor, 0805 Pkg. |
| L1 | Inductor, 0603 Pkg. |
| U1 | HMC311ST89(E) |
| PCB [2] | 107368 Evaluation PCB |

[1] Reference this number when ordering complete evaluation PCB

[2] Circuit Board Material: Rogers 4350

The circuit board used in the final application should use RF circuit design techniques. Signal lines should have 50 Ohm impedance while the package ground leads and package bottom should be connected directly to the ground plane similar to that shown. A sufficient number of via holes should be used to connect the top and bottom ground planes. The evaluation board should be mounted to an appropriate heat sink. The evaluation circuit board shown is available from Hittite upon request.

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.