

29511 Composite - 1000V UL Flexible Motor Supply Cable



For more Information
please call

1-800-Belden1



General Description:

1 pr.(Signal)-16 AWG stranded (26x30) TC cond., XLPE insul., Beldfoil® shield (100% c), drain; 3 cond.(VFD) plus 1 ground wire-14 AWG stranded (41x30) TC cond., XLPE insul., Duofoil® and TC braid Shield (100% a85% c), drain, PVC jacket.

Usage (Overall)

Suitable Applications: AC Motor Drive, VFD, Variable Frequency Drive

Twisted Pair

Physical Characteristics

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
1	16	26x30	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
XLPE - Cross Linked Polyethylene	0.030

Twisted Pair Color Code Chart:

Number	Color
1	Black and White

Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG	Stranding	Conductor Material
18	19x30	TC - Tinnecc Copper

Electrical Characteristics

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
34.000

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
4.000

Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
4.990

Multi Conductor

Physical Characteristics

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
3	14	41x30	TC - Tinned Copper

Ground Wire

Ground Wire (Y/N): Yes

Ground Wire Material:

AWG	Stranding	Conductor Material	Insulation Material
14	41x30	TC - Tinned Copper	PVC - Polyvinyl Chloride

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
---------------------	----------------------

29511 Composite - 1000V UL Flexible Motor Supply Cable

XLPE - Cross Linked Polyethylene	0.045
----------------------------------	-------

Insulation Color Code Chart:

Number	Color
1	Black #1
2	Black #2
3	Black #3
4	Green/Yellow

Individual Shield

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100.000
2		Braid	TC - Tinned Copper	85.000

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
14	41x30	TC - Tinned Copper

Electrical Characteristics

Nom. Inductance:

Inductance (µH/ft)
0.213

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
42.000

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
23.000

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
2.520

Physical Characteristics (Overall)

Conductor

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.075

Outer Jacket Ripcord: Yes

Overall Cable

Overall Nominal Diameter: 0.820 in.

Mechanical Characteristics (Overall)

Max. Recommended Pulling Tension: 368 lbs.

Min. Bend Radius/Minor Axis: 8.200 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: RHW-2 Singles, TC-ER, XHHW-2

NEC Articles: 335 - ER

CEC/C(UL) Specification: 600V Type CIC TC

CSA Specification: 1000 V AWM I/II A/B

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 09/21/2006

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

29511 Composite - 1000V UL Flexible Motor Supply Cable

PMSHA Specification:	P-07-KA070003
Other Specification:	1000V UL Flexible Motor Supply Cable

Flame Test

UL Flame Test:	UL1685 UL Loading
CSA Flame Test:	FT4
IEEE Flame Test:	1202, IEEE 383 Vertical Tray Flame Test (70,000 BTU)

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Burial:	Yes
Sunlight Resistance:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
----------------------	----

Electrical Characteristics (Overall)

Max. Operating Voltage - UL:

Voltage

1000 V RMS (Flexible Motor Supply Cable)

Max. Operating Voltage - Other:

Voltage

1000 V RMS (CSA AWM I/II A/B)

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
29511 010100	100 FT	67.500 LB	BLACK	C	COMPOSITE CABLE SH PVC
29511 0101000	1,000 FT	340.000 LB	BLACK	C	COMPOSITE CABLE SH PVC
29511 010500	500 FT	177.500 LB	BLACK	C	COMPOSITE CABLE SH PVC
29511 0105000	5,000 FT	1,565.000 LB	BLACK	C	COMPOSITE CABLE SH PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 08-20-2013

© 2016 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).