



Main

Range	ClimaSys
Product name	ClimaSys CV
Product or component type	Fan
Type of ventilation filter	Standard
Air flow	Free flow rate with standard filter : 350 m ³ /h at 60 Hz Free flow rate with standard filter : 300 m ³ /h at 50 Hz
[Us] rated supply voltage	75...126 V
Input voltage	115 V 50/60 Hz

Complementary

Rated power in W	36 W 50 Hz 36 W 60 Hz
[In] rated current	0.35 A 50 Hz 0.32 A 60 Hz
Noise level	55...56 dB
Bearing type	Ball
Height	External : 268 mm
Width	External : 248 mm
Depth	External : 116 mm
Cut-out dimensions	223 x 223 mm
Product weight	1.3 kg
Material	Injected thermoplastic (ASA PC) for outlet grille
Colour	Outlet grille : grey RAL 7035
Ambient air temperature for operation	-10...70 °C
Ambient air temperature for storage	-40...70 °C
Maximum pressure	158 Pa flow rate 0 m ³ /h
Connections - terminals	Faston connector
IP degree of protection	IP54

Device composition	<ul style="list-style-type: none"> 1 outlet grille front 1 axial motor 2 protective grille on the front and rear surfaces 1 filter front of axial motor 1 cut-out template 1 power cord
Condition of use	<ul style="list-style-type: none"> Surrounding environment must be relatively clean Overfrequent filter replacement should be avoided Filter must be cleaned and replaced regularly Flow rates depends on the work point, see ProClima software Outside temperature must be 5 °C lower than inside temperature

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------