

TM2AMM6HT
analog input/output module M238 - 4 inputs
voltage/current high level - 2 output



Main

Range of product	Modicon M238 logic controller
Product or component type	Input/Output analog module
Analogue input number	4
Input level	High level
Analogue input type	Current 4...20 mA non differential Voltage 0...10 V non differential
Analogue output number	2
Analogue output type	Current 4...20 mA Voltage 0...10 V
Cross talk	≤ 2 LSB

Complementary

Range compatibility	Advantys OTB Twido
Analogue input resolution	12 bits
Analogue output resolution	12 bits
LSB value	2.5 mV voltage voltage 4 μ A current current
Permissible continuous overload	13 V voltage 40 mA current
Input impedance	≤ 250 MOhm current ≥ 1 Ohm voltage
Load type	Resistive
Load impedance ohmic	≤ 300 Ohm current ≥ 2000 Ohm voltage
Stabilisation time	20 ms
Conversion time	20 ms + 1 controller cycle time
Sampling duration	≤ 16 ms
Acquisition period	16 ms per channel + 1 controller cycle time

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Measurement error	+/- 0.5 % of full scale 0...10 V 25 °C +/- 0.5 % of full scale 4...20 mA 25 °C +/- 0.9 % of full scale 0...10 V 25 °C +/- 0.9 % of full scale 4...20 mA 25 °C
Temperature coefficient	+/- 0.02 %FS/°C 0...10 V +/- 0.02 %FS/°C 4...20 mA +/-0.015 %FS/°C 0...10 V 0...10 V +/-0.015 %FS/°C 4...20 mA 4...20 mA
Repeat accuracy	+/- 1 %FS output +/-0.5 %FS input
Non-linearity	+/- 0.4 %FS current +/- 0.4 %FS voltage +/- 0.5 %FS current +/- 0.5 %FS voltage
Output error	+/- 1 %FS
Output ripple	<= 1 LSB
Total error	+/- 1.5 %FS current +/- 1.5 %FS voltage +/-1 %FS current current +/-1 %FS voltage voltage
Type of cable	Shielded cable
Insulation between channel and internal logic	Photocoupler
Supply	External supply
[Us] rated supply voltage	24 V DC
Supply voltage limits	19.2...30 V
Electrical connection	1 removable screw terminal block
Current consumption	60 mA 5 V DC internal 80 mA 24 V DC external
Product weight	0.085 kg

Environment

Dielectric strength	1500 V between the I/O and the external supply circuit 800 V between I/O channel 800 V between the I/O and internal logic
Width	23.5 mm
Depth	70 mm
Height	90 mm

Offer Sustainability


Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1039 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product environmental
Product end of life instructions	Available End of life manual

Contractual warranty

Warranty period	18 months
-----------------	-----------


Analog Mixed I/O Module (6-channel, Voltage/Current)

Dimensions



NOTE: * 8.5 mm (0.33 in) when the clip-on lock is pulled out.

DIN Rail Mounting




Rail depth	Catalogue part number
15 mm (0.59 in.)	AM1DE200
7,5 mm (0.30 in.)	AM1DP200

NOTE: Do not use AM1ED200 and DZ5MB200







Module Mounting on a Panel Surface

Mounting Hole Layout




Wiring Requirements

Cable Types and Wire Sizes for Removable Screw Terminal Block

							
mm ²	0,14...1,5	0,25...0,5	0,25...1,5	0,14...0,5	0,14...0,75	0,25...0,34	0,5
AWG	26...16	24...20	24...16	26...20	26...18	24...22	20

Analog Mixed I/O Module (6-channel, Voltage/Current)

Wiring Diagram



- (1) Voltage preactuator
- (2) Current preactuator