

LC1K0910M7

TeSys K contactor - 3P - AC-3 \leq 440 V 9 A - 1
NO aux. - 220...230 V AC coil



Main

Range of product	TeSys K
Range	TeSys
Product or component type	Contacteur
Product name	TeSys K
Device application	Control
Contacteur application	Resistive load Motor control

Complementary

Utilisation category	AC-4 AC-3 AC-1
Poles description	3P
Pole contact composition	3 NO
[Ie] rated operational current	9 A at \leq 440 V AC AC-3 for power circuit 20 A (\leq 50 °C) at \leq 440 V AC AC-1 for power circuit 16 A (\leq 70 °C) at 690 V AC AC-1 for power circuit
Control circuit type	AC 50/60 Hz
Control circuit voltage	220...230 V AC 50/60 Hz
Motor power kW	2.2 kW at 400 V AC 50/60 Hz AC-4 2.2 kW at 220...230 V AC 50/60 Hz AC-3 4 kW at 380...415 V AC 50/60 Hz AC-3 4 kW at 440 V AC 50/60 Hz AC-3 4 kW at 480 V AC 50/60 Hz AC-3 4 kW at 500...600 V AC 50/60 Hz AC-3 4 kW at 660...690 V AC 50/60 Hz AC-3
Auxiliary contact composition	1 NO
Overvoltage category	III
[Ith] conventional free air thermal current	20 A at \leq 50 °C for power circuit 10 A at \leq 50 °C for signalling circuit
Irms rated making capacity	110 A AC for power circuit conforming to NF C 63-110

	110 A AC for power circuit conforming to IEC 60947 110 A AC for signalling circuit conforming to IEC 60947
Rated breaking capacity	110 A at 415 V conforming to IEC 60947 110 A at 440 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 110 A at 220...230 V conforming to IEC 60947 110 A at 380...400 V conforming to IEC 60947 70 A at 660...690 V conforming to IEC 60947
Associated fuse rating	25 A gG at <= 440 V for power circuit 25 A aM for power circuit 10 A gG for signalling circuit conforming to IEC 60947 10 A gG for signalling circuit conforming to VDE 0660
Average impedance	3 mOhm at 50 Hz - lth 20 A for power circuit
Insulation resistance	> 10 MOhm for signalling circuit
Inrush power in VA	30 VA at 20 °C
Hold-in power consumption in VA	4.5 VA at 20 °C
Heat dissipation	1.3 W
Control circuit voltage limits	0.2...0.75 Uc at <= 50 °C drop-out 0.8...1.15 Uc at <= 50 °C operational
Operating rate	3600 cyc/h
Auxiliary contacts type	Type instantaneous (1 NO)
Signalling circuit frequency	<= 400 Hz
Minimum switching current	5 mA for signalling circuit
Minimum switching voltage	17 V for signalling circuit
Operating time	10...20 ms coil de-energisation and NO opening 10...20 ms coil energisation and NO closing
Safety reliability level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Non overlap distance	0.5 mm
Mechanical robustness	Shocks contactor closed, on X axis 10 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed, on Y axis 15 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed, on Z axis 15 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on X axis 6 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on Y axis 10 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on Z axis 10 Gn for 11 ms IEC 60068-2-27 Vibrations contactor closed 4 Gn, 5...300 Hz IEC 60068-2-6 Vibrations contactor opened 2 Gn, 5...300 Hz IEC 60068-2-6

Environment

Product certifications	CSA UL
Protective treatment	TC conforming to IEC 60068 TC conforming to DIN 50016
Operating altitude	2000 m without derating in temperature
Flame retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0633 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product environmental
Product end of life instructions	Available End of life manual

Contractual warranty

Warranty period	18 months
-----------------	-----------