



Main

Range of product	Modicon M241
Product or component type	Analogue input cartridge
Product specific application	Hoisting applications
Product compatibility	Modicon M241C
Analogue input number	2

Complementary

Analogue input type	Current, input range: 4...20 mA Current, input range: 0...20 mA Voltage, input range: 0...10 V
Analogue input resolution	16 bits
LSB value	1 mV (voltage), output range: 0...10 V 2 µA (current), output range: 0...20 mA 2 µA (current), output range: 4...20 mA
Sampling duration	10 ms
Absolute accuracy error	+/- 0.2 % of full scale at 25 °C
Temperature drift	+/- 0.006 %FS/°C
Repeat accuracy	+/- 0.2 %FS
Non-linearity	+/- 0.05 %FS
Cross talk	80 dB
Type of cable	Twisted shielded pairs cable
Electrical connection	1 spring terminal block (pitch 3.81 mm) 1.5 mm ² 1 for inputs and supply
Cable length	<= 30 m twisted shielded pairs cable (input)
Insulation	Non-insulated between inputs Between input and internal logic 500 V DC
Supply voltage limits	20.4...28.8 V
Local signalling	1 LED green PWR
Height	50 mm
Depth	21 mm
Width	34 mm

Product weight	0.055 kg
Permissible continuous overload	40 mA (current) 30 V (voltage)
Input impedance	<= 250 Ohm current >= 1 MOhm voltage

Environment

Immunity to microbreaks	10 ms
-------------------------	-------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1350 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available  Product environmental
Product end of life instructions	Available  End of life manual