

# LAD6K10B

## CONTACTOR MECH. LATCH CONTACT BLOCK

### IEC



#### Main

Range	TeSys
Product or component type	Mechanical latch block
Product compatibility	LC1DT60A...DT80A TeSys D control relays LC1D40A...D65A LC1DT20...DT40 LC1D09...D38
Control circuit voltage	24 V AC 50/60 Hz 24 V DC

#### Complementary

Mounting location	Front side
Tripping control	Manual Electrical
[Ui] rated insulation voltage	690 V - conforming to IEC 60947-5-1
Power required in VA	25 for AC circuit
Power required in W	30 W for DC circuit
Mechanical durability	500000 cycles
Operating rate	1200 cyc/h
On-load factor	10 %
Product weight	0.07 kg

#### Environment

Product certifications	UL CSA
IP degree of protection	IP2x conforming to VDE 0106
Protective treatment	TH conforming to IEC 60068
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

Contractual warranty

Warranty period	18 months
-----------------	-----------