



For more Information  
please call

1-800-Belden1



### General Description:

Security & Commercial Audio Cable, Riser-CMR, 3-20 AWG stranded bare copper conductors with polyolefin insulation, Beldfoil® shield and PVC jacket with ripcord

### Usage (Overall)

Suitable Applications: Intercom/PA Systems, Sound/Audio Systems

### Physical Characteristics (Overall)

#### Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
3	20	7x28	BC - Bare Copper

Total Number of Conductors: 3

#### Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PP - Polypropylene	0.008

#### Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape w/Shorting Fold	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
24	Solid	TC - Tinned Copper

#### Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.017

Outer Jacket Ripcord: Yes

### Overall Cable

Overall Cabling Lay Length & Direction:

Length (in.)	Direction	Twists (twist/ft)
2.500	Left Hand	4.800

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	Red
3	White

Overall Nominal Diameter: 0.149 in.

### Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 17 lbs/1000 ft.

Max. Recommended Pulling Tension: 46.900 lbs.

Min. Bend Radius/Minor Axis: 1.500 in.

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMR

NEC Articles: 800

## 5401FE Multi-Conductor - Commercial Audio Systems

CEC/C(UL) Specification:	CMG
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes

### Flame Test

UL Flame Test:	UL1666 Vertical Shaft
C(UL) Flame Test:	FT4

### Suitability

Suitability - Indoor:	Yes
-----------------------	-----

### Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	6401FE

## Surface Printing (Overall)

## Electrical Characteristics (Overall)

### Nom. Inductance:

**Inductance (µH/ft)**

### Nom. Capacitance Conductor to Conductor:

**Capacitance (pF/ft)**

### Nom. Capacitance Cond. to Other Conductor & Shield:

**Capacitance (pF/ft)**

### Nom. Conductor DC Resistance:

**DCR @ 20°C (Ohm/1000 ft)**

### Nominal Outer Shield DC Resistance:

**DCR @ 20°C (Ohm/1000 ft)**

### Max. Operating Voltage - UL:

**Voltage**

### Max. Recommended Current:

**Current**

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5401FE 008U1000	1,000 FT	19.000 LB	GRAY		3 #20 PP FS FRPVC
5401FE 008U500	500 FT	9.500 LB	GRAY		3 #20 PP FS FRPVC
5401FE 0081000	1,000 FT	18.000 LB	GRAY	C	3 #20 PP FS FRPVC
5401FE 008500	500 FT	9.500 LB	GRAY		3 #20 PP FS FRPVC

### Notes:

C = CRATE REEL PUT-UP.

## 5401FE Multi-Conductor - Commercial Audio Systems

Revision Number: 3    Revision Date: 08-19-2013

© 2017 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).