

## AX101433 Faceplates and Panels - Interface Plate 2 Port Single Gang Flush



For more Information  
please call

1-800-Belden1



### General Description:

Interface Plates 2 Port, Single Gang Flush

### Usage (Overall)

|                               |   |
|-------------------------------|---|
| <b>Suitable Applications:</b> | - Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800,3600, 2400 and 1200. |
| <b>Related Parts:</b>         | - Compatible with 10GX, CAT6+ and CAT5E MDVO-style Modular Jacks and MDVO Multimedia Modules                              |

### Physical Characteristics (Connectivity)

#### Capacity

|                       |         |
|-----------------------|---------|
| <b>Max. Capacity:</b> | 2 ports |
|-----------------------|---------|

#### Access

|                          |       |
|--------------------------|-------|
| <b>Front Connection:</b> | Flush |
|--------------------------|-------|

#### Dimensions

Dimensions:

| Height (in.) | Width (in.) | Depth (in.) |
|--------------|-------------|-------------|
| 4.490        | 3.000       | 0.460       |

#### Materials

Materials:

| Description | Material          |
|-------------|-------------------|
| Plate       | Plastic - UL94V-0 |

#### Color

|               |       |
|---------------|-------|
| <b>Color:</b> | White |
|---------------|-------|

#### Weight

|                |            |
|----------------|------------|
| <b>Weight:</b> | 0.110 lbs. |
|----------------|------------|

#### Included Parts

|                        |   |
|------------------------|---|
| <b>Included Parts:</b> | blank, 6-32 screw, carton label, clear window, installation sheet |
|------------------------|---|

#### Packaging

|                   |   |
|-------------------|---|
| <b>Packaging:</b> | Individually packaged in a plastic bag. |
|-------------------|---|

### Mechanical Characteristics (Connectivity)

|  |                |
|--|----------------|
| <b>Connector/Hardware Retention:</b>   | 20 lbs.        |
| <b>Storage Temperature Range:</b>      | -40°C To +70°C |
| <b>Installation Temperature Range:</b> | -10°C To +60°C |
| <b>Operating Temperature Range:</b>    | -10°C To +60°C |

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

|  |                                  |
|--|----------------------------------|
| <b>EU Directive 2002/95/EC (RoHS):</b>       | Yes                              |
| <b>EU RoHS Compliance Date (mm/dd/yyyy):</b> | 07/01/2006                       |
| <b>MII Order #39 (China RoHS):</b>           | EUP 50                           |
| <b>Safety Listing:</b>                       | ACA, Bi-national Standard Listed |

#### Suitability

|                              |     |
|------------------------------|-----|
| <b>Suitability - Indoor:</b> | Yes |
|------------------------------|-----|

### Transmission Characteristics (Connectivity)

### Notes (Overall)

**Notes:** For proper installation refer to Installation Guide PX101806 included with the product or visit our web site at <http://www.belden.com>

## AX101433 Faceplates and Panels - Interface Plate 2 Port Single Gang Flush

### Product Family

Part Numbers:

| Description                               | Gray     | Almond   | White    | Black    | Ivory    |
|---|----------|----------|----------|----------|----------|
| Interface Plate Flush 2-port Single Gang  | AX101431 | AX101432 | AX101433 | AX101434 | AX102582 |
| Interface Plate Flush 4-port Single Gang  | AX101435 | AX101436 | AX101437 | AX101438 | AX102583 |
| Interface Plate Flush 6-port Single Gang  | AX101439 | AX101440 | AX101441 | AX101442 | AX102584 |
| Interface Surface Adapter Box Single gang | AX101474 | AX101475 | AX101476 | AX101477 | AX102589 |

### Put Ups and Colors:

| Item #   | Putup | Ship Weight | Color | Notes | Item Desc                     |
|----------|-------|-------------|-------|-------|-------------------------------|
| AX101433 | 1 EA  | 0.038 KG    |       |       | INTERFACE PLATE 2-PORT SG WHI |

Revision Number: 0    Revision Date: 06-02-2009

© 2017 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.