



### Main

Range of product	Modicon Quantum automation platform
Product or component type	RIO drop adaptor module

### Complementary

Product compatibility	Quantum
Number of I/O expansion module	<= 27
Type of cable	Coaxial 75 Ohm
Transmission rate	1544 Mbit/s
Dynamic range	35 dB
Isolation voltage	500 V DC coaxial center and ground
Electrical connection	2 female connectors F elbowed with redundant cable
Diagnostics startup	Power up and runtime RAM address/data Executive checksum
Power dissipation in W	3.8 W 2 channels
Bus current requirement	750 mA 2 channels
Module format	Standard

### Environment

Standards	UL 508 CUL CSA C22.2 No 142
Resistance to electrostatic discharge	4 kV contact conforming to IEC 801-2 8 kV on air conforming to IEC 801-2
Resistance to electromagnetic fields	10 V/m 80...1000 MHz conforming to IEC 801-3
Ambient air temperature for operation	0...60 °C
Ambient air temperature for storage	-40...85 °C
Relative humidity	95 % without condensation

---

Operating altitude	<= 5000 m
--------------------	-----------

---

**Offer Sustainability**

---

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0901 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product environmental</a>
Product end of life instructions	Available <a href="#">End of life manual</a>

---

**Contractual warranty**


---

Warranty period	18 months
-----------------	-----------

---

Racks for Modules Mounting

Dimensions of Modules and Racks



- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots