



Taper and deburring countersinkers DIN 334 type C 60° HSS

Packing unit: in plastic tubes of 1

Steel (N/mm ²) < 900	<input checked="" type="checkbox"/>	Brass	<input checked="" type="checkbox"/>
Steel (N/mm ²) < 1100	<input type="checkbox"/>	Bronze	<input type="checkbox"/>
Steel (N/mm ²) < 1300	<input type="checkbox"/>	Plastics	<input checked="" type="checkbox"/>
Rust-resistant steel	<input type="checkbox"/>	Cast iron	<input type="checkbox"/>
Aluminium	<input checked="" type="checkbox"/>	Titanium alloyed	<input type="checkbox"/>

Ø2 mm	Ø1 mm	L1 mm	Ø3 mm	HSS		
6,3	1,6	45,0	5,0	102 201	1	
8,0	2,0	50,0	6,0	102 202	1	
10,0	2,5	50,0	6,0	102 203	1	
12,5	3,2	56,0	8,0	102 204	1	
16,0	4,0	63,0	10,0	102 205	1	
20,0	5,0	67,0	10,0	102 206	1	
25,0	6,3	71,0	10,0	102 207	1	



Taper and deburring countersinkers DIN 334 type D 60° HSS

Packing unit: in plastic tubes of 1

Steel (N/mm ²) < 900	<input checked="" type="checkbox"/>	Brass	<input checked="" type="checkbox"/>
Steel (N/mm ²) < 1100	<input type="checkbox"/>	Bronze	<input type="checkbox"/>
Steel (N/mm ²) < 1300	<input type="checkbox"/>	Plastics	<input checked="" type="checkbox"/>
Rust-resistant steel	<input type="checkbox"/>	Cast iron	<input type="checkbox"/>
Aluminium	<input checked="" type="checkbox"/>	Titanium alloyed	<input type="checkbox"/>

Ø2 mm	Ø1 mm	L1 mm	Shank S1	HSS		
16,0	4,0	90,0	MT 1	102 208	1	
20,0	5,0	106,0	MT 2	102 209	1	
25,0	6,3	112,0	MT 2	102 210	1	
31,5	10,0	118,0	MT 2	102 211	1	
40,0	12,5	150,0	MT 3	102 212	1	
50,0	16,0	160,0	MT 3	102 213	1	
63,0	20,0	190,0	MT 4	102 214	1	
80,0	25,0	200,0	MT 4	102 215	1	

