

# PFA Coated Thermocouple Probes

## With Standard Size Connectors

**We Can PFA Coat Most Thermocouple Probes. Contact Our Sales Department for Availability and Price.**



- ✓ Chemically Inert
- ✓ Electrically Insulated
- ✓ Rated to 205°C (400°F)
- ✓ Quick-Disconnect Style
- ✓ 1.5 mm (1/16") or 3.0 mm (1/8") Diameter
- ✓ Grounded Junction
- ✓ 300 mm (12") Probe Standard†
- ✓ 0.010 PFA Coating (Typical)

PFA coated probes are the perfect solution when there is a need to measure the temperature of caustic or corrosive chemical solutions in industrial and laboratory environments. The superior corrosion resistance of PFA allows you to measure the temperature of sulfuric, hydrochloric, nitric, and chromic acids, as well as caustic compounds.

- Applications**
- ✓ Battery Electrolyte
  - ✓ Plating Baths
  - ✓ Anodizing Baths
  - ✓ Severe Environments



All products shown smaller than actual size.

HDX probe handle not included. Please see [omega.com/sdx\\_hdx\\_probes](http://omega.com/sdx_hdx_probes) of probe handles.

**Note:** OMEGA can pre-bend PFA coated probes prior to shipping. Consult Sales for this option. Probes ordered from this page are shipped straight.

To Order		
Calibration	Probe Dia.* mm (inch)	Model Number
Iron-Constantan <b>J</b>	1.5 (1/16)	ICSS-116G-12-PFA
	1.5 (1/16)	ICSS-116G-18-PFA
	1.5 (1/16)	ICSS-116G-24-PFA
	6.0 (1/4)	ICSS-14G-12-PFA
	6.0 (1/4)	ICSS-14G-18-PFA
	6.0 (1/4)	ICSS-14G-24-PFA
	3.0 (1/8)	ICSS-18G-12-PFA
	3.0 (1/8)	ICSS-18G-18-PFA
	3.0 (1/8)	ICSS-18G-24-PFA
CHROME <sup>®</sup> GA <sup>®</sup> -ALOMEGA <sup>®</sup> <b>K</b>	1.5 (1/16)	CASS-116G-12-PFA
	1.5 (1/16)	CASS-116G-18-PFA
	1.5 (1/16)	CASS-116G-24-PFA
	3.0 (1/8)	CASS-18G-12-PFA
	3.0 (1/8)	CASS-18G-18-PFA
	3.0 (1/8)	CASS-18G-24-PFA
Copper-Constantan <b>T</b>	1.5 (1/16)	CPSS-116G-12-PFA
	1.5 (1/16)	CPSS-116G-18-PFA
	1.5 (1/16)	CPSS-116G-24-PFA
	3.0 (1/8)	CPSS-18G-12-PFA
	3.0 (1/8)	CPSS-18G-18-PFA
	3.0 (1/8)	CPSS-18G-24-PFA
CHROME <sup>®</sup> GA <sup>®</sup> -Constantan <b>E</b>	1.5 (1/16)	CXSS-116G-12-PFA
	1.5 (1/16)	CXSS-116G-18-PFA
	1.5 (1/16)	CXSS-116G-24-PFA
	3.0 (1/8)	CXSS-18G-12-PFA
	3.0 (1/8)	CXSS-18G-18-PFA
	3.0 (1/8)	CXSS-18G-24-PFA

Standard size connectors, shown smaller than actual size.



Mating connector, cable clamp and locking clip included.

Available in lengths up to 1.2 m (4').

\* Before PFA coating. † Other lengths available, consult Sales department.  
Ordering Example: CASS-18G-12-PFA, coated thermocouple probe, Type K, stainless steel sheath, 3 mm (1/8") Dia., grounded, 300 mm (12") long.